





Circuit Diagram



NOTES:

1.ELECTCAL CHARACTERISTICS:

- 1-1.CONTACT CURRENT RATING: 50mA.
- 1-2.CONTACT VOLTAGE RATING: 12V. DC.
- 1-3.CONTACT RESISTANCE: 100mΩ MAX.
- 1-4.DIELECTRIC WITHSTANDING VOLTAGE: 250V. AC.
- 1-5.INSULATION RESISTANCE: 100 MΩ MIN.

2.MECHANICAL CHARACTERISTICS:

- 2-1.DURABILITY: 100,000 CYCLES.
- 2-2.TRAVEL: 0.45±0.20mm.

3.ENVIRENMENT CHARACTERISTICS:

- 3-1.OPERATING TEMPERATURE: -40°C~+85°C
- 3-2.HUMIDITY: 45-85% RH.

NO.1	
PART NO	vigor
1	100±30

NO.2-NO.3	
PART NO	NOTE
01~99	SERIAL NUMBER

⑤	Terminal	—	3	Phosphor Bronze	Plating silver	—
④	Contact	—	1	SUS	Plating silver	—
③	Base	—	1	PPA	Black	—
②	Cover	—	1	Phosphor Bronze	Plating silver	—
①	Knob	—	1	Silica gel	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE				
DRAWN	LIUCAN	2021.6.1					
CHECKED				TITLE:	TACT SWITCHS		
APPROVALS				PART NO.	K2-1852SP-A□SW-□□		
TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 	
	10~30	±0.20					
	5~10	±0.15					
	~ 5	±0.10					
			±2'	DRAWING NO.	_____	SHEET 1 OF 1	

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.