




HX30001-2P



技术要求Specification:

- 1、材质Material: Rubber shell:PA66 UL94V-2(0)
- 2、额定电流Current rating: 5A max
- 3、额定电压 Voltage rating: 250V AC/DC
- 4、温度范围 Temperature range:-25℃to+105℃
- 5、接触电阻 Contact resistance:≤15mΩ
- 6、绝缘电阻 Insulation resistance:≥1000MΩ
- 7、耐压 Withstand voltage:1000V AC/minute
- 8、适配的端子 Adaptable terminals:HX30001-PT
- 9、适配的插座/针座 Adaptable receptacle/Wafer: HX30001-R/HX30001-A

B	6.8	9.8	12.8	15.8	18.8	21.8	24.8	27.8	30.8	33.8	36.8
A	3.0	6.0	9.0	12.0	15.0	18.0	21.0	24.0	27.0	30.0	33.0
孔数	2	3	4	5	6	7	8	9	10	11	12

未注公差表 UNTOLERANCE TABLE		设计 DRAWN BY	王鹏程	产品名称 PRODUCT NAME	插头 Plug Housing
≤3	± 0.1	审核 CHECKED BY	郑建银	产品型号 PRODUCT MODEL	43645-*P
≤10	± 0.2				
≤20	± 0.35	批准 APPROVED BY	沈才义	红星代号 HONGXING NO	HX30001-*P
≤35	± 0.4				
≤50	± 0.5	日期 DATE	2020.06.08	浙江红星电业有限公司 Zhejiang Hongxing Electrical Co., Ltd.	
≤75	± 0.6	视图 VIEW	单位 UNIT		
≤100	± 0.8	mm	页码 SHEET		
ANGLE	± 5°	mm	1/1		