



Lead-Free Current Sensing Resistors RLPL12 (Halogen-Free)

Document No	TRLPL-120S001A
Issued date	2017/06/02
page	1/8


1. Scope :

This specification applied to the products of Lead-Free current sensing resistor of metal strip for Lead-Free RLPL12 manufactured by TA-I TECHNOLOGY CO.,LTD.

2. Type Designation :

RLPL12	F	E	G	M	R040
Series No.	Tolerance	Packaging	Power	Material	Resistance
L12→1225	F = $\pm 1\%$ G = $\pm 2\%$ J = $\pm 5\%$	E=Embossed	G = 3W	M = MnCu	R040=40mΩ

3. Construction and Dimension :



Series	L	W	D	T
RLPL12	3.20±0.3	6.40±0.30	0.5±0.20	0.9 ±0.25

UNIT: mm



Lead-Free Current Sensing Resistors RLPL12 (Halogen-Free)

Document No	TRLPL-120S001A
Issued date	2017/06/02
page	2/8

4. Features:

Series	Size	Power (W)	Resistance Value	Operation Temperature Range	TCR	Tolerance
RLPL12	1225	3.0	2~40 mΩ	-55℃~+170℃	±75ppm/℃	±1% ±2% ±5%

5. Reliability Tests:


Test Items	Reference standard	Condition of Test	Test Limits
Temperature Coefficient of Resistance	IEC60115-1-4.8 JIS-C5201-4.8	+25℃ ~ +125℃	Refer 4.0
Load Life	IEC60115-1-4.25.1 JIS-C5201-4.25.1	1000hours at rated power, 70℃, 1.5hours "ON", 0.5hour "OFF"	< ±1%
Short Time Overload	IEC60115-1-4.13 JIS-C5201-4.13	5 X rated power for 5s	< ±1%
Moisture no Load	IEC60115-1- 4.24.2.1a) JIS-C5201- 4.24.2.1a)	85℃, 85%RH, 1000hrs	< ±1%
Temperature cycle	IEC60115-1-4.19 JIS-C5201-4.19	-55℃ & +155℃, 300cycle, 15min per extreme condition	< ±1%
Resistance to Soldering Heat	IEC60115-1-4.18 JIS-C5201-4.18	260±5℃ for 10±1 sec	< ±0.5%
Solderability	IEC60115-1-4.17 JIS-C5201-4.17	245±5℃, 2±0.5sec	At least 95% of surface area of electrode shall be covered with new solder
High Temperature Exposure	IEC60115-1- 4.23.2 JIS-C5201-4.23.2	170℃, 1000hrs	< ±1%
Low Temperature Storage	IEC60115-1- 4.23.4 JIS-C5201-4.23.4	-55℃, 1000hrs	<±1%
Substrate Bending	IEC60115-1-4.33 JIS-C5201-4.33	Bending width 2mm	< ±0.5%
Insulation Resistance	IEC60115-1-4.6 JIS-C5201-4.6	100V DC for 1 minute	>100 MΩ



Lead-Free Current Sensing Resistors RLPL12 (Halogen-Free)

Document No	TRLPL-120S001A
Issued date	2017/06/02
page	3/8

5.1 Derating Curve



5.2 Rated Current & Voltage

The rated Current and Voltage are calculated by the following formula:

$$I = \sqrt{P \div R}$$

$$V = \sqrt{P \times R}$$

I: Rated Current (A)

V: Rated Voltage (V)

P: Rated Power (W)


R: Resistance Value (Ω)



Lead-Free Current Sensing Resistors RLPL12 (Halogen-Free)

Document No	TRLPL-120S001A
Issued date	2017/06/02
page	4/8

6. Recommended Solder Pad Dimension



Unit: mm

Series	Resistance (mΩ)	A	B	L
RLPL12	2 ~ 40	7.0	1.0	2.3

Note: *The copper foil minimum thickness of PCB needs 3 oz




Lead-Free Current Sensing Resistors RLPL12 (Halogen-Free)

Document No	TRLPL-120S001A
Issued date	2017/06/02
page	5/8


7. Number of Package:

Series	RLPL12
Pieces/Package	4000

8. Label:



9. Packaging



Embossed tape packaging dimension


Symbol	A ₀	B ₀	W	E	F	P ₀	P ₁	P ₁	D ₀	K ₀	T
RLPL12	3.60	6.90	12.00	1.75	5.50	4.00	4.00	4.00	2.00	1.20	0.30
Tolerance	±0.20	±0.20	±0.20	±0.10	±0.10	±0.10	±0.10	±0.10	±0.10	±0.15	±0.10



Lead-Free Current Sensing Resistors RLPL12 (Halogen-Free)

Document No	TRLPL-120S001A
Issued date	2017/06/02
page	6/8


10. Reel Specification



Series	ϕA	ϕB	ϕC	W	T
RLPL12	178 $\pm$ 2.0	60 $\pm$ 1.0	13.0 $\pm$ 1.0	13.0 $\pm$ 1.0	15.4 $\pm$ 1.0

11. Peeling Strength of Top Cover Tape

Test Condition: 0.1 to 0.7 N at a peel-off speed of 300 mm / min.



12. Storage Conditions:

Temperature: 5°C~35°C, Humidity: 40%~75%

13. Shelf Life:


2 years from manufacturing date.



Lead-Free Current Sensing Resistors RLPL12 (Halogen-Free)

Document No	TRLPL-120S001A
Issued date	2017/06/02
page	7/8

14. Recommend IR – Reflow profile : (solder : Sn96.5 / Ag3 / Cu0.5)



Alloyed Re-flow times : 3 times

Remark : To avoid discoloration phenomena of chip on terminal electrodes, please use N2 Re-flow furnace .

Iron Solder: $350 \pm 10^{\circ}\text{C}$, 3+1/-0 sec, 1 time


Profile Feature	Lead (Pb)-Free Assembly
Average ramp-up rate (Tsmax to Tp)	3°C / second max.
Preheat - Temperature Min (Tsmmin) - Temperature Max (Tsmmax) - Time (Tsmmin to Tsmmax) (ts)	150°C 200°C 60 -150 seconds
Time maintained above : - Temperature (Tl) - Time (Tl)	217°C 60-120 seconds
Peak Temperature (Tp)	260°C
Time within $+0^{\circ}\text{C}$ of actual Peak Temperature (tp) ²	10 seconds
Ramp-down Rate	6°C/second max.
Time 25°C to Peak Temperature	8minutes max.



Lead-Free Current Sensing Resistors RLPL12 (Halogen-Free)

Document No	TRLPL-120S001A
Issued date	2017/06/02
page	8/8

15. Recommend Wave-Solder profile : (solder : Sn96.5 / Ag3 / Cu0.5)



16. ECN

Engineering Change Notice: The customer will be informed with ECN if there is significant modification on the characteristics and materials described in Approval Sheet.

17. Manufacturing Country & City :

TA-I TECHNOLOGY CO., LTD. (Taiwan– Tao Yuan)

Tel : (+886) 3-3246169 Fax : (+886) 3-3246167

Associated companies :

(1)TA-I TECHNOLOGY (SU ZHOU) CO., LTD. (China – Su Zhou)

Tel :(+86) 512-63457879 Fax : (+86) 512-63457869

(2) TA-I TECHNOLOGY ELECTRONIC (DONGGUAN) CO., LTD. (China –Dongguan)

Tel : (+86) 769-8339-4790~3 Fax : (+86) 769-8339-4794

(3) FORTUNE TASK RESISTOR FACTORY (China – Dongguan)

Tel : (+86) 769-8339-4790~3 Fax : (+86) 769-8339-4794

(4) TAI OHM ELECTRONICS (M) SDN. BHD. (Malaysia – Penang)

Tel :(+60) 4- 3900480 Fax : (+60) 4-3901481

(5) P.T.TAI ELECTRONIC Indonesia (Indonesia – Jakarta)

Tel :(+62) 21-44820254 Fax : (+62) 21-44820256