





REV.	ECN Number	Description	Drawn
1	CS19040073	RELEASE	2019. 04. 18



SECTION: A-A

NOTES:

1. HOUSING MATERIAL:HIGH TEMPERATURE PLASTICS, UL94V-0.
2. CONTACT MATERIAL:COPPER ALLOY.
3. OPERATING TEMPERATURE RANGE: $-40^{\circ}\text{C}\sim+105^{\circ}\text{C}$
4. STORAGE TEMPERATURE RANGE: $-40^{\circ}\text{C}\sim+105^{\circ}\text{C}$
5. Harmful Material Should Comply With The "RoHS2.0" Standard.
6. "▽" SIZE FOR CPK;
7. PRODUCT NUMBER MATRIX:





APC6-32XX-X-X

WTB
Power supply seat
2.20 pitch
T/H, V/T
Pin number
32=32pin
Contact Plating:


TYPE	DESCRIPTION
0	With clip, high temperature plastics, black
1	Without Clip, high temperature plastics, black
2	With Clip, high temperature plastics, Natural

Definition	Code
◎ Matte Tin plated	A
◎ Gold plated over all	
Flash B	1u" R 3u" C
5u" D	10u" E 15u" F
20u" G	25u" H 30u" J


NULL:Low temperature thermoplastic
F:High temperature thermoplastic
H:Halogen free
T:Tray
K:REEL



DETAIL B
SCALE 10: 1



DETAIL A
SCALE 8: 1



ShenZhen ShenTai wxiang Electronics Co., Ltd.

TOLERANCE UNLESS OTHERWISE SPECIFIED

X. X	±0.30	X. °	±3°
X. XX	±0.20	X. X°	±2°
X. XXX		X. XX°	±1°

SCALE 1:1

UNIT mm

SIZE A4



ORIGINAL DRAWN:

CJ

DATE 2019. 04. 18

CHECK:

XPG

DATE 2019. 04. 18

APPROVE:

Ady zhou

DATE 2019. 04. 18

DWG. NO.

600-0000-0456

PARTS NO. (INTENDED USE)

APC6-32XX-X-X

TITLE





PH2.2-32PIN DIP CONNECTOR
CUSTOMER DRAWING

REV.

1

SHEET

1/2

 PAD AREA

 BSTEEL MESH HOLE



ShenZhen ShenTai weixiang Electronics Co., Ltd.

TOLERANCE UNLESS OTHERWISE SPECIFIED				SCALE 1:1		ORIGINAL DRAWN: CJ		DATE 2019. 04. 18		DWG. NO. 600-0000-0456		TITLE PH2. 2-32PIN DIP CONNECTOR CUSTOMER DRAWING		REV. 1	
X. X	±0.30	X. °	±3°	UNIT mm		CHECK: XPG		DATE 2019. 04. 18						SHEET	
X. XX	±0.20	X. X°	±2°	SIZE A4		APPROVE: Ady zhou		DATE 2019. 04. 18		PARTS NO. (INTENDED USE) APC6-32XX-X-X				2/2	
X. XXX		X. XX°	±1°												