






CAD FILE:



RATING: DC 50V 0.3A

8					TOLERANCE UNLESS SPECIFIED						
7											
6						WITHIN:1.5mm±0.1mm OVER :1.5mm±0.2mm					
5	SPRING	SUS	1	TEMPER	ISSUE		DATE	DESCRIPTIONS			APPD.
4	CAM STICK	SUS	1	NATURAL	TITLE : Horizontal Slide Switch			UNIT :MM	DRWG NO.:		
3	INSERT CASE	NYLON+F.G/BRASS STRIP	1	GREY/Ag PLATED OVER Ni PLATED							
2	COVER	POM	1	BLACK/WHITE	MODEL: SK13D07VG5			SCALE:5:1	DWN		
1	INSERT KNOB	POM/PBS C5210R-EH	1	WHITE/Ag CLAD					CHK'D		
NO.	PART NAME	MATERIAL	Q'TY	FINISHING	深圳市逸致电子有限公司 Shenzhen Yizhi Electronics Co.,LTD				APPD.		