

PRODUCT NO.	1	2	3	4	5	6
DSIC04LSGER	RoHS compliant					




REV.	ECN NO.	DR	DATE

- NOTES :
- Specification:
 - Operating force:1000gf Max
 - Operating Temperature: -40° to+85°
 - Storage Temperature: -40° to+85°
 - Mechanical Life: 3000cycles minimum
 - Electrical Life: 2000cycles minimum
 - PLATING:



GOLD FLASH 1u"~2u" SOLDER TAIL, 1u"~3u" GOLD PLATING ON THE CONTACT AREA, WITH 50u" NICKEL UNDERPLATING OVERALL.

3. PART NUMBER DESCRIPTION


DSIC	XX	L	S	G	E	R	
							[包装方式: T=管装 R=Reel]
							[电镀层: E=接触部 1u"~3u" /焊接部 1u"~2u"]
							[G=镀金 S=内金外镍]
							[脚型: S脚 / J脚 / H脚 / A脚 / Z脚]
							[T=低推贴胶 S=低推不贴胶 L=长推]
							[产品P数: 02=2P 08=8P 10=10P 12=12P]




[Schematic]



RECOMMENDED P.C.B. LAYOUT (TOP VIEW)



(Construction)



Number	Part Name	Material	Finished
①	Actuator	UL94 V0	White
②	Cover	UL94 V0	Black
③	Movable	Copper Alloy	1u"~3u"Gold
④	Terminal	Brass	1u"~2u"Gold
⑤	Base	UL94 V0	Black
⑥	Terminal Contact	Brass	1u"~3u"Gold

TOLERANCE UNLESS OTHERWISE SPECIFIED	
LINER	ANGLES
.0 ± 0.25	0. ± 2°
.00 ± 0.15	.0 ± 1°
.000± 0.10	.00± 0.5°
DESIGN	kathy
DRAWING	
CHECK	
APPRO.	

INSPECTION	COPY
PROJECTION	
2012/04/12	

东莞市广普实业有限公司 DongGuan Kingtek Industrial Co., Ltd.			
TITLE BY DSIC SERIES PITCH 2.54mm			
PRODUCT FAMILY DSIC SERIES			
PRAT NO. DSIC04LSGER			
FILE NO. DSIC04LSGER-A			
SIZE	UNIT	SCALE	SHEET
A4	mm	2 : 1	1 OF 1
			REV. A