




1 2 3 4 5 6 7 8 9


G

G



SPECIFICATIONS

Current Rating: 1.5 Amps
 Insulation Resistance: 1000M Ω , Min
 Contact Resistance: 20m Ω , Max
 Withstanding Voltage: AC 500V
 Operation Temperature: -40° to +105°
 Contact Material: Brass
 Standard: PA6T
 Insulator Material: Polyester (UL 94V-0)
 Contact Plating: Gold Flash
 Max. Processing Temp: 240° C for 30–60 seconds
 (260° C for 5 seconds)



RECOMMEND P. C. B LAYOUT

PCB TOLERANCE: ±0.05 (TOP VIEW)



®
深圳市韩下电子有限公司

UNLESS OTHERWISE SPECIFIED TOLERANCE

X : ±0.30 X° : ±5°
 X.X : ±0.25 X.X° : ±1°
 X.XX : ±0.20 X.XX° : ±0.5°

DRAWN NAME: HX IDC200-2-07-S-5.7

| | | | | | |
|------|----|-------|-----|------------|----------|
| SIZE | A4 | SCALE | N:1 | PROUCT NO. | |
| REV | A | UNIT | mm | PROJECT | PAGE 1/1 |

DRAWN: 黄彬 2020.6.24 CHECKED: 张伟 2020.6.24 APPROVED: 罗小春 2020.6.24

| No. of | DIM. A | DIM. B | No. of | DIM. A | DIM. B | No. of | DIM. A | DIM. B | No. of | DIM. A | DIM. B |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 6 | 4.00 | 6.00 | 24 | 22.00 | 24.00 | 42 | 40.00 | 42.00 | 60 | 58.00 | 60.00 |
| 8 | 6.00 | 8.00 | 26 | 24.00 | 26.00 | 44 | 42.00 | 44.00 | 62 | 60.00 | 62.00 |
| 10 | 8.00 | 10.00 | 28 | 26.00 | 28.00 | 46 | 44.00 | 46.00 | 64 | 62.00 | 64.00 |
| 12 | 10.00 | 12.00 | 30 | 28.00 | 30.00 | 48 | 46.00 | 48.00 | 66 | 64.00 | 66.00 |
| 14 | 12.00 | 14.00 | 32 | 30.00 | 32.00 | 50 | 48.00 | 50.00 | 68 | 66.00 | 68.00 |
| 16 | 14.00 | 16.00 | 34 | 32.00 | 34.00 | 52 | 50.00 | 52.00 | 70 | 68.00 | 70.00 |
| 18 | 16.00 | 18.00 | 36 | 34.00 | 36.00 | 54 | 52.00 | 54.00 | | | |
| 20 | 18.00 | 20.00 | 38 | 36.00 | 38.00 | 56 | 54.00 | 56.00 | | | |
| 22 | 20.00 | 22.00 | 40 | 38.00 | 40.00 | 58 | 56.00 | 58.00 | | | |

1

2

3

4

5

6

7

8

9

A

B

D

E

F

G