

1. Features

- Built-in bias resistors enable the configuration of an inverter circuit without connecting external input resistors(see equivalent circuit);
- The bias resistors consist of thin-film resistors with complete isolation to allow negative biasing of the input.They also have the advantage of almost completely eliminating parasitic effects;
- Only the on/off conditions need to be set for operation, making device design easy.






2.MAXIMUM RATINGS (Ta=25℃ unless otherwise noted)

Parameter	Symbol	Limits (DTC114E xx)						Unit
		M	E	UA	CA	KA	SA	
Supply Voltage	V_{CC}	50						V
Input Voltage	V_{IN}	-10~+40						V
Output Current	I_O	100						mA
Power Dissipation	P_D	100	150	200	200	200	300	mW
Operation Junction and Storage Temperature Range	T_J, T_{stg}	-55~+150						℃







3. Electrical Characteristics (Ta=25℃ unless otherwise specified)

Symbol	Parameter	Condition	Min	Typ	Max	Unit
R ₁	Input resistance		7	10	13	kΩ
R ₂ /R ₁	Resistance ratio		0.8	1	1.2	
V _{O(on)}	Output voltage	I _O /I _I =10mA/0.5mA	—	—	0.3	V
I _I	Input current	V _I =5V	—	—	0.88	mA
I _{O(off)}	Output current	V _{CC} =50V, V _I =0	—	—	0.5	μA
G ₁	DC current gain	V _O =5V, I _O =5mA	30	—	—	
V _{I(off)}	Input voltage	V _{CC} =5V, I _O =100μA	0.5	—	—	V
V _{I(on)}		V _O =0.3V, I _O =10mA	—	—	3	V
f _T	Transition frequency	V _O =10V, I _O =5mA, f=100MHz	—	250	—	MHz

4. Pinning information


Pin	symbol	Part Number	Simplified outline	Equivalent Circuit	Marking	Package
1	IN	DTC114ECA			24	SOT-23
2	GND					
3	OUT					
1	IN	DTC114EKA			24	SOT-23-3
2	GND					
3	OUT					
1	IN	DTC114EE			24	SOT-523
2	GND					
3	OUT					
1	IN	DTC114EUA			24 •	SOT-323
2	GND					
3	OUT					

5. Electrical Characteristics Diagrams




6 . Outline Drawing

SOT-23 Package Outline Dimensions



Symbol	Dimensions In Millimeters		
	Min	Typ	Max
A	0.65		1.40
A1	0.00		0.20
b	0.30		0.55
c	0.08		0.20
D	2.70		3.10
E	1.15		1.65
E1	2.10		2.80
e	1.70		2.10
L	0.15		0.50
L1	0.35		0.70
θ	0°		12°

7 . Suggested Pad Layout



- Note:
1. Controlling dimension: in/millimeters.
 2. General tolerance: $\pm 0.05\text{mm}$.
 3. The pad layout is for reference purposes only.

8. Important Notice and Disclaimer

Microdiode Electronics (Shenzhen) reserves the right to make changes to this document and its products and specifications at any time without notice. Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.

Microdiode Electronics (Shenzhen) makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Microdiode Electronics (Shenzhen) assume any liability for application assistance or customer product design. Microdiode Electronics (Shenzhen) does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application.

No license is granted by implication or otherwise under any intellectual property rights of Microdiode Electronics (Shenzhen).

Microdiode Electronics (Shenzhen) products are not authorized for use as critical components in life support devices or systems without express written approval of Microdiode Electronics (Shenzhen).