



深圳市兴华鑫电子科技有限公司

Shenzhen xinghuaxin Electronic Technology Co., Ltd

承認書

SPECIFICATION FOR APPROVAL

客戶 (Customer):

客戶料號 (Customer P/N):

興華鑫型號 (Supplier P/N):

3410BOX-8 Ω 1W-2P1.25

產品名稱 (Description):

喇叭 (Speaker)

產品規格 (Specification):

34*10MM 2P1.25 端子

客戶承認欄 (Customer Authorization Signature)	深圳市興華鑫電子科技有限公司 承認欄 (Supplier Audit)		
	審核	檢查	制作
	唐国兴	唐玉来	吴银娟
	日期: 2024 年 12 月 30 日 版次: A		

声音让生活更精彩!

地址: 深圳市宝安区新安街道新乐社区新乐路 88 号厂房四层

TEL: 0755-27892904

E-mail: jacky.tang@jsxhxdz.com

Http: www.jsxhxdz.com


產品規格內容 (SPECIFICATION)

Model	No.	XHXDZ-3410 腔体喇叭	Date	2024-12-30	Page No.	1 / 6
1.使用範圍 (Scope) 此份規格書是針對多媒體產品內，所使用的微型揚聲器單體所提出的報告。 This specification covers our product of miniature speaker unit for multimedia product. 2.标准测试条件(Test condition) 一般规格试验状态（特殊要求除外）：常温 5~35℃，常湿 45%~85%，气压 860~1060hPa. 判定上有疑问时，试验状态为：温度 20±2℃，相对湿度 60%~70%，气压 860~1060 hPa. The test conditions unless otherwise specified should be normal temperature 5 to 35 ℃,Normal humidity 45 to 85% and normal atmospheric pressure 860 to 1060 hPa,However,if there arises a doubt in judgment,the test conditions shall beas follows: Temperature 20±2℃ Humidity 60%~70% Atmosphere 860~1060 hPa 3.電聲特性 (ELECTRO-ACOUSTIC CHARACTERISTICS) 3.1 額定阻抗(Rated Impedance): 8.0Ω ± 20% (AT 1.6K Hz ,1.0 Vrms) 3.2 額定輸入功率(Rated Input Power) 1.0 Watt (At 2.83 Vrms white noise 96 Hours) 3.3 最大輸入功率(Max. Input Power) 1.2 Watt 3.4 最低共振頻率(Resonant Frequency) 1060 Hz ± 20% 3.5 輸出音壓(Output S.P.L) 96± 3dB (0.1 Watt , 0.1 Meter. Average at 0.8K,1.0K,1.5K,2.0K Hz) 3.6 實效頻率範圍(Frequency Range) Fo ~ 20KHz (By Output S.P.L. -10dB) 3.7 失真率(Distortion) Less than 5% (At 1.6KHz , 0.894 Vrms) 3.8 工作溫度(Operating Temperature) -25℃ ~ +50℃ 3. 9 儲存溫度(Storage temperature) -25℃ ~ +55℃						
制 定		审 核		核 准		文 件 编 号
吴银娟		唐玉来		唐国兴		

Model No.	XHXDZ-3410 腔体喇叭	Date	2024-12-30	Page No.	2 / 6
-----------	-----------------	------	------------	----------	-------

4.可靠性測試 (Reliability Test)

4.1 高低溫差循環測試(Temperature Cycling Test)



A	Low Temperature (-25°C±3°C)	
B	High Temperature (+55°C±3°C)	
C	Number of Cycle (3 Cycles)	
D	Duration of Exposure 1 Hours, at Each Temperature Extremes	
E	Duration of Recovery 1 Hours	

4.2 抗濕度試驗(Humidity Test)

A	相對濕度(Relative Humidity)	90-95% at + 40°C ± 3°C
B	測試時間(Durations)	96 Hours
C	恢復時間(Durations of recovery)	6 Hours

4.3 連續負載測試(Load Test)

White Noise Without Weighted Filter 2.83Volts.(RMS) 100 Hrs.

4.4 跌落試驗(Drop Test)

75 cm Free Falling On Concrete Floor, 10 Times.

4.5 異常音測試(Buzzes & Rattles)



Sine wave between at 2.2Vrms / 200~5000Hz

4.6 極性測試(Polarity test)

Diaphragm Shall Move Forward When Apply a Positive DC. Current to the “+”or “Marked” Terminal.

Model No.	XHXDZ-3410 腔体喇叭	Date	2024-12-30	Page No.	3 / 6
-----------	-----------------	------	------------	----------	-------


5.測量方式 (Measurement Method)




產品規格內容 (SPECIFICATION)

Model No.	XHXDZ-3410 腔体喇叭	Date	2024-12-30	Page No.	4/6
-----------	-----------------	------	------------	----------	-----

6. 頻率響應曲線圖(Frequency Response Curve)



7. 阻抗曲線圖(Impedance Curve)




產品規格內容 (SPECIFICATION)

Model No.	XHXDZ-3410 腔体喇叭	Date	2024-12-30	Page No.	5 / 6
-----------	-----------------	------	------------	----------	-------

8. 喇叭外觀描述

(Unit:mm tolerance:±0.3)



產品規格內容 (SPECIFICATION)

Model No.	XHXDZ-3410 腔体喇叭	Date	2024-12-30	Page No.	6/6
-----------	-----------------	------	------------	----------	-----

9.包裝示意圖(Packing Standard):
(Unit:cm tolerance:±3)

PACKING STANDARD:

