

POLYMER PTC RESETTABLE FUSE




Part Number: TLC-MSMD300/8

1、Physical Dimensions(size of 1812)

Unit:mm

Part Number	A		B		C		D	Marking
	Min	Max	Min	Max	Min	Max	Min	
TLC-MSMD300/8	4.37	4.73	3.07	3.41	0.60	1.00	0.30	T300



2、Electrical Characteristics

Part Number	I _H (A)	I _T (A)	V _{max} (V)	I _{max} (A)	T _{trip} (Max time to trip)		P _{d typ} (W)	R _{min} (Ω)	R _{1max} (Ω)
					Current(A)	Time(S)			
TLC-MSMD300/8	3.00	6.00	8	100	8.0	5.00	1.2	0.012	0.060

I_H: Holding Current: maximum current at which the device will not trip in 25°C still air.

I_T: Tripping Current minimum current at which the device will trip in 25°C still air.

V_{max}: Maximum voltage device can withstand without damage at rated current.

I_{max}: Maximum fault current device can withstand without damage at rated voltage.

T_{trip}: Maximum time to trip(s) at assigned current.

P_{d typ}: Rated working power.

R_{min}: Minimum resistance of device prior to trip at 25°C.



R_{1max}: Maximum resistance of device is measured one hours post reflow at 25°C.

Notes: All electrical function test is conducted after PCB mounted.

3、Thermal Derating

TLC-MSMD300/8	Maximum ambient operating temperature								
	-40°C	-20°C	0°C	25°C	40°C	50°C	60°C	70°C	85°C
Hold Current(A)	4.40	3.90	3.50	3.00	2.60	2.30	2.10	1.80	1.50
Trip Current(A)	8.80	7.80	7.00	6.00	5.20	4.60	4.20	3.60	3.00

4、Solder Reflow Recommendations



Notes: If reflow temperatures exceed the recommended profile, devices may not meet the performance requirements.

5、Package Information

Packing quantity: 1500PCS/Reel

Note: Reel packaging per EIA-481-1 standard

6、Agency Recognition: TUV



Caution: Operation beyond the rated voltage or current may result in rupture electrical arcing or flame. Specifications are subject to change without notice.

TEL: 86-0769-3892 0554 FAX: 86-0769-8793 2077 E-mail: Tina@tlcet.com.cn

Address: No.18, 5th GaoLi Road, TangXia Town, DongGuan, GuangDong, P.R China 523710