









3D轴测图



P.C.B LAYOUT



H=XXmm

SPECIFICATION

- 1.Rating : DC12V 50mA.
- 2.Contact resistance: $\leq 100\text{m}\Omega$.
- 3.Insulation resistance: $\geq 100\text{M}\Omega$ (DC100V).
- 4.Withstanding voltage: 250VAC .
- 5.Operating Force: $160\pm 50\text{gf}/250\pm 80\text{gf}$ (依客户需求而定) .
- 6.life test: 50,000 cycles.
- 7.Operation temperature range: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
- 8.Sign "*" is importance dimension.

					TOLERANCE UNLESS SPECIFIED						
6	COVER	SUS	1		<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°	A1	2023.5.17	更新图纸		WM
5	KNOB	LCP	1	BLACK			NO	DATE	REVISIONS		BY APPD
4	DUSTPROOF FILM	PI	1	YELLOW	TITLE: TACT SWITCH			UNIT : MM	ROHS	DWN	
3	SPRING	SUS	2	AG-PLATED	MODEL: TS-1185-025C-01-L			SCALE: 1:1	COMPLIANT	CHK'D	
2	CASE	LCP	1		 皓宇 HOOYA			DONGGUANG HAOYU ELECTRONICS CO., LTD			APPD
1	CARD	PHOSPHOR BRONZE	1	AG-PLATED				东莞市弘皓电子有限公司			PRO.AGL:  
NO.	PART	NAME	MATERIAL	QTY	FINISHING						