






REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



焊脚尺寸以顺畅过孔规为准



8	—
7	—
6	RX-
5	—
4	—
3	RX+
2	TX-
1	TX+
PIN	说明

NOTES

MATERIAL

- 1.HOUSING MATERIAL: LCP UL94V-0 BLACK.
- 2.CONTACT MATERIAL: PHOSPHOR BRONZE $\phi 0.46\text{mm}$.
- 3.PLATING: GOLD FLASH PLATING OVER NICKEL.

ELECTRICAL


- 1.VOLTAGE RATING: 125 VAC RMS.
- 2.CURRENT RATING: 1.5 AMP.
- 3.CONTACT RESISTANCE: 40 MILLIOHMS MAX.
- 4.INSULATION RESISTANCE: 500 MEGOHMS MIN @ 100V DC .
- 5.DIELECTRIC DIELECTRIC RESISTANCE: 500V DC RMS 50Hz. 1MIN.


MECHANICAL

- 1.DURRABILITY: 750 CYCLES MIN.
- 2.MATING/UNMATING FORC: 3.06 Kgf MAX.
- 3.RETENTION STRENGTH: 5.1 Kgf MIN.

ENVIRONMENTAL:

- 1.STORAGE: $-40^{\circ}\sim+85^{\circ}$.
- 2.OPERATION: $-40^{\circ}\sim+85^{\circ}$.
- 3.REFLOW TEMPERATURE: $260\pm 5^{\circ}$ 3~5 S



TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.:±0.35	X':±3"	PART NO. RJ45-A004-8P	TITLE: RJ45 56型C嵌全翘无灯2.2脚LCP黑		
X.X:±0.25	X.X':±2"				
X.XX:±0.15	X.XX':±1"				
UNITS	mm	DESIGN:	Ethan	MANUFACTURE DWG	
MATERILA	— — —	CHED:	Olvia		SCALE
FINISH	— — —	APPD:	Ava		SHEET
				N:A	1/1