








RATING: DC 50V 0.5A

8					TOLERANCE UNLESS SPECIFIED				
7									
6					WITHIN:1.5mm±0.1mm OVER :1.5mm±0.2mm				
5	SPRING	SUS	1	TEMPER		ISSUE	DATE	DESCRIPTIONS	APPD.
4	CAM STICK	SUS	1	NATURAL	TITLE : Horizontal Slide Switch			UNIT :MM	
3	INSERT CASE	NYLON+F.G/BRASS STRIP	1	GREY/Ag PLATED OVER Ni PLATED				DRWG NO.:	
2	COVER	POM	1	BLACK/WHITE	MODEL: SK12F14G6			SCALE:5:1	DWN
1	INSERT KNOB	POM/PBS C5210R-EH	1	WHITE/Ag CLAD				SCALE:5:1	CHK'D
NO.	PART NAME	MATERIAL	Q'TY	FINISHING	深圳市逸致电子有限公司 Shenzhen Yizhi Electronics Co.,LTD			APPD.	