









Switching:25mA at 24VDC
Non-Switching:100mA at 50VDC
Initial:50m Ω Max
After life:100m Ω Max
Insulation Resistance:100m Ω Min,60 sec at 500VDC
Dielectric Strength:500VAC for 60seconds
Switch Capacitance:5pF Max at 1MHZ
Operation Temperature:-30°C to + 85°C
Storage Temperature:-40°C to + 85°C
Operation Force:500gf Max
Mechanical Life:3000 cycles operations
Resistance to Soldering:260 $\pm$ 5°C for 3-5 seconds




Poles(N)	A Dimension(mm)
01	2.54
02	5.08
03	7.62
04	10.16
05	12.70
06	15.24
07	17.78
08	20.32
09	22.86
10	25.40
12	30.48



SCHEMATIC

Part Name	Material	Finished
Base	PPS UL94 VO	Black
Cover	PPS UL94 VO	Black
Actuator	Nylon UL94 VO	White
Movadle	Copper Alloy	Gold
Terminal Contact	Brass	Gold
Terminal	Brass	Gold/Tin

A4				 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJCTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TSD112EZ
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw		
A1					ROCPCU TECHNOLOGY CO.,LTD						
REV	DATE	REVISION	DESCRIPTION								ISSUE
								Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission			
A		B		C		D	E		F		G