

N-Ch 150V Fast Switching MOSFETs
General Description


- 100% EAS Guaranteed
- Green Device Available
- Super Low $R_{DS(ON)}$
- Advanced high cell density Trench technology

Applications

- Load Switch
- LED Applications
- PWM Application
- Power Managenmet

Product Summary

V_{DS}	150	V
$R_{DS(ON),typ}$	8.1	m Ω
I_D	90	A

TO-220 Pin Configuration

Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	150	V
V_{GS}	Gate-Source Voltage	± 20	V
$I_D@T_C=25^{\circ}C$	Continuous Drain Current, $V_{GS} @ 10V^{1,6}$	90	A
$I_D@T_C=100^{\circ}C$	Continuous Drain Current, $V_{GS} @ 10V^{1,6}$	61	A
I_{DM}	Pulsed Drain Current ²	350	A
EAS	Single Pulse Avalanche Energy ³	530	mJ
$P_D@T_C=25^{\circ}C$	Total Power Dissipation ⁴	150	W
T_{STG}	Storage Temperature Range	-55 to 150	$^{\circ}C$
T_J	Operating Junction Temperature Range	-55 to 150	$^{\circ}C$

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JA}$	Thermal Resistance Junction-Ambient ¹	---	28	$^{\circ}C/W$
$R_{\theta JC}$	Thermal Resistance Junction-Case ¹	---	0.7	$^{\circ}C/W$

N-Ch 150V Fast Switching MOSFETs
Electrical Characteristics ($T_J=25\text{ }^{\circ}\text{C}$, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V$, $I_D=250\mu A$	150	---	---	V
$R_{DS(ON)}$	Static Drain-Source On-Resistance ²	$V_{GS}=10V$, $I_D=20A$	---	8.1	10	m Ω
$V_{GS(th)}$	Gate Threshold Voltage	$V_{GS}=V_{DS}$, $I_D=250\mu A$	2	3	4	V
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=120V$, $V_{GS}=0V$, $T_J=25^{\circ}\text{C}$	---	---	1	μA
		$V_{DS}=120V$, $V_{GS}=0V$, $T_J=125^{\circ}\text{C}$	---	---	5	
I_{GSS}	Gate-Source Leakage Current	$V_{GS}=\pm 20V$, $V_{DS}=0V$	---	---	± 100	nA
R_g	Gate Resistance	$V_{DS}=0V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	3.6	---	Ω
Q_g	Total Gate Charge	$V_{DS}=75V$, $V_{GS}=10V$, $I_D=20A$	---	50	---	nC
Q_{gs}	Gate-Source Charge		---	19	---	
Q_{gd}	Gate-Drain Charge		---	14	---	
$T_d(on)$	Turn-On Delay Time	$V_{DD}=75V$, $V_{GS}=10V$, $R_G=2.7\Omega$, $I_D=10A$	---	17	---	ns
T_r	Rise Time		---	45	---	
$T_d(off)$	Turn-Off Delay Time		---	48	---	
T_f	Fall Time		---	39	---	
C_{iss}	Input Capacitance	$V_{DS}=75V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	3380	---	pF
C_{oss}	Output Capacitance		---	321	---	
C_{rss}	Reverse Transfer Capacitance		---	15	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_S	Continuous Source Current ^{1,5}	$V_G=V_D=0V$, Force Current	---	---	90	A
V_{SD}	Diode Forward Voltage ²	$V_{GS}=0V$, $I_S=1A$, $T_J=25^{\circ}\text{C}$	---	---	1.2	V
t_{rr}	Reverse Recovery Time	$I_f=20A$, $di/dt=100A/\mu s$, $T_J=25^{\circ}\text{C}$	---	86	---	nS
Q_{rr}	Reverse Recovery Charge		---	251	---	nC

Note :

1.The data tested by surface mounted on a 1 inch² FR-4 board with 20Z copper.

2.The data tested by pulsed , pulse width $\leq 300\mu s$, duty cycle $\leq 2\%$

3.The EAS data shows Max. rating . The test condition is $V_{DD}=75V$, $V_{GS}=10V$, $L=3mH$, $I_{AS}=19A$

4.The power dissipation is limited by 150°C junction temperature

5.The data is theoretically the same as I_D and I_{DM} , in real applications , should be limited by total power dissipation.

6.Package limitation current.

Typical Characteristics

Figure 1: Power De-rating




Figure 2: Current De-rating




Figure 3: Normalized Maximum Transient Thermal Impedance




Figure 4: Peak Current Capacity




Figure 5: Output Characteristics




Figure 6: Typical Transfer Characteristics




Figure 7: On-resistance vs. Drain Current




Figure 8: Body Diode Characteristics




Figure 9: Gate Charge Characteristics





Figure 10: Capacitance Characteristics



N-Ch 150V Fast Switching MOSFETs

Figure 11: Normalized Breakdown voltage vs. Junction Temperature




Figure 12: Normalized on Resistance vs. Junction Temperature




Figure 13: Normalized Threshold Voltage vs. Junction Temperature




Figure 14: $R_{DS(ON)}$ vs. V_{GS}






Figure 15: Maximum Safe Operating Area





TO-220 Package Information



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max
A	4.300	4.700	0.169	0.185
A1	2.200	2.600	0.087	0.102
b	0.700	0.950	0.028	0.037
b1	1.170	1.410	0.046	0.056
c	0.450	0.650	0.018	0.026
c1	1.200	1.400	0.047	0.055
D	9.600	10.400	0.378	0.409
E	8.8500	9.750	0.348	0.384
E1	12.650	12.950	0.498	0.510
e	2.540 TYP.		0.100TYP.	
e1	4.980	5.180	0.196	0.204
F	2.650	2.950	0.104	0.116
H	7.900	8.100	0.311	0.319
h	0.000	0.300	0.000	0.012
L	12.750	14.300	0.502	0.563
L1	2.850	3.950	0.112	0.156
V	7.500 REF.		0.295 REF.	
Φ	3.400	4.000	0.134	0.157