

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.08.09	阿树

备注 NOTES:

1.材质 Material:

1.1 胶芯 Plastic core: LCP

1.2 端子 Terminal: C18140, T=0.15mm: Nickel base,gold plated

1.3 外壳 shell: SUS, T=0.30mm: Nickel plated on the surface

1.4 卡片 shell fragment: SUS, T=0.15mm:

2. 电气特性 ELECTRICAL CHARACTERISTIC:

2.1 额定电流 Rated current: 5A

2.2 接触阻抗 Contact resistance: 40mΩ MAX

2.3 绝缘阻抗 Insulation resistance: 100MΩ MIN 250V DC

2.4 耐压 WITHSTANDING VOLTAGE: 100V AC

2.5 沾锡性: 温度245±5℃, 时间5±0.5s

2.6 插入力INSERTION FORCE: 2.0kgf MAX

拔出力 EXTRACTION FORCE:0.6kgf MIN

2.7 使用寿命 Service life: 10,000次

2.8 工作温度 Operating temperature: -40℃~+120℃

U264-24XN-4BSK00

03:AU 3U"Min
30:AU 30U"Min

A1	GND	B12	GND
A2	SSTXP1	B11	SSRXP1
A3	SSTXN1	B10	SSRXN1
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	SSRXN2	B3	SSTXN2
A11	SSRXP2	B2	SSTXP2
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEWS	MODEL TYPE: Type-C 3.1
CHECKED		UNIT: mm/in	PART NO.: U264-24XN-4BSK00
APPROVED		SIZE: A4	DWG NO.:
		SCALE	PAGE
		N/A	1/1
		REVISION	A1

XKB INDUSTRIAL PRECISION CO.,LIMITED