

DATA SHEET

SUNGMUN CODE : SSI-10H-OR0

DESCRIPTION : MINI SLIDE SWITCH

SUNGMUN ELECTRONICS CO., LTD.

Address 301-302,Bucheon Technopark 345, Seokcheon-ro, Ojeong-gu
Bucheon-si, Gyeonggi-do, Korea
TEL. +82-32-328-1941~4
FAX +82-32-328-1945
E-mail sungmun@sungmun.co.kr
Website www.sungmun.com










SUNGMUN
ELECTRONICS

REV NO.	DATE	REVISION	DR	CH	APP

SPECIFICATION



- Rating : DC12V 0.5A~24V 0.3A.
- Contact Resistance : 30mΩ Max.
- Travel : 1.6mm.
- Operating Force : 250 ± 150gf.
- Life Cycle : 2,000 Cycle (with load).
- Packing : 200pcs Vinyl Bag
- Body Color : Orange



DRAW/DESIGNED	CHECKED	APPROVED		G.TOL	TITLE	MINI SLIDE SWITCH
K.N KIM	W.J LEE	K.I LEE		± 0.3	MODEL NO.	SSI-10H-ORO
2022-10-19	2022-10-19	2022-10-19		UNIT mm	SCALE 3:1	REV.
SUNGMUN ELECTRONICS CO.,LTD				SIZE A4	DRAW NO.	SSI-10H-ORO-01
						01

REV NO.	DATE	REVISION	DR	CH	APP
	22.10.11	모델명 변경(BSI->SSI) 및 색상코드 & 성문 로고 추가	K.N KIM	W.J LEE	K.I LEE

MINI SLIDE SWITCH CODE [SSI-10 TYPE]



01	-		-		-		-	
NO.	DESCRIPTION			MATERIAL		COLOR / FINISH		REMARK
	DRAW/DESIGNED	CHECKED	APPROVED		G.TOL ±0.3	TITLE	MINI SLIDE SWITCH	
	S.M PARK	W.J LEE	K.I LEE	UNIT	SCALE	MODEL NO.	SSIX-10XX-XXXX-XX	
	2019-11-01	2019-11-01	2019-11-01	mm	N:S		REV.	
	 SUNGMUN ELECTRONICS CO.,LTD				SIZE	DRAW NO.	SSIX-10XX-XXXX-XX-11	
					A4		11	

1. Electrical Characteristics :

- 1.1 Rating : AC, DC 12V 0.5A~24V 0.3A (Minimum current: 1mA)
- 1.2 Contact Resistance : Max 30 mΩ
- 1.3 Insulation Resistance : Min 10,000 MΩ at DC 500V
- 1.4 Withstanding Voltage : 1min at AC 500V

2. Mechanical Characteristics :

- 2.1 Operating Force : 250gf ± 150gf
- 2.2 Travel : 1.6mm
- 2.3 Insulator :
 - 2.3.1 Case : Glass Fiber resin
 - 2.3.2 Slide : Glass Fiber resin
- 2.4 Terminal : Nickel, Gold Plate

3. Life Test :

- 3.1 Test Condition : Operations at a rate of 15-20 cycles in 1 minute
 - 3.1.1 With load : 2,000 cycles
 - 3.1.2 Without load : 10,000 cycles
- 3.2 Operating Force : With +40%, -40% of Initial Value
- 3.3 Contact Resistance : Max 200mΩ

4. Environmental Characteristics :

- 4.1 Operating Temperature : -40°C to +85°C
- 4.2 Storage Temperature : -40°C to +85°C
- 4.3 Humidity Test :
 - 4.3.1 Test Conditions : Measured 1hour after exposure to ambient
After 96hours exposure at 40±2°C, 90-95%R.H
 - 4.3.2 Insulation Resistance : Min 100MΩ, at DC 500V
 - 4.3.3 Withstanding Voltage : 1min at AC 250V

5. Solder Conditions :

- 5.1 Hand Solder : 3~4 sec. at 350°C
- 5.2 Wave Solder : 5 sec. at 260°C