


Kinghelm®

REVISIONS					
REV	NUMBER	DESCRIPTION	DWN	CHK	DATE
A		DESIGN			



NOTES:

- ELECTRICAL:
 - VOLTAGE RATING:DCV 300V 10MS
 - CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
 - INSULATION RESISTANCE: 5.0M OHM/MIN.
 - THE CABLE SHOULD BE 100% ELECTRICAL TEST
 - IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.
- MATERIAL:
 - SEE TABLE
- MECHANICALL:
 - SMA PULL FORCE: 12.0KGS.
- ALL COMPONENTS ARE RoHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
④	套管	黑色热缩套管，OD:2.0MM	AS
③	端子	高仿I-PEX，1.37端子，镀金	1
②	接头	SMA母头内孔，分体，11牙，镀金	1
①	同轴线	RF 1.37黑色线，OD:1.37mm	AS

深圳市金航标电子有限公司 WWW.BDS666.COM

KH- IPEX-SMA-RG137-100MM **0755-83044319**

ALL DIMENSION ARE IN MM	DRAWN Jamy	DATE 2018 /05 /04				
	ENG.		TITLE RF CABLE I-PEX1.37 TO SMA /F L=100 MM			
	MFG.					
	Q.A.					
COMPUTER GENERATED IN SOLIDWORKS			SIZE	Number		REV
DO NOT SCALE THIS DRAWING			B			A
PROJECTION	GENERAL TOLERANCE FOR ANGLES X.X X.XX X.XXX ± 1° ± 0.3 ± 0.25 ± 0.150		SCALE: Free		TYPE	SHEET 1 OF 1
						