








标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE



3D VIEW



RECOMMEND PCB LAYOUT(±0.05)

NOTES:

- MATERIAL:
 - HOUSING: LCP, COLOR IS GRAY, HIGH TEMPERATURE PLASTIC;
 - CONTACT: BRASS (H65 T=0.20mm);
 - SHELL: COLD ROLLED IRON (SPCC, T=0.50mm);
- FINISH:
 - TERMINAL:
CONTACT AREA: GOLD PLATED G/Fu";
SOLDER AREA: PLATED OVER TIN;
 - SHELL: NI PLATED OVER ALL ;
- ELECTRICAL:
 - VOLTAGE RATING: 40 VAC RMS;
 - CURRENT RATING: 0.5 AMP;
 - CONTACT RESISTANCE: 30mΩ MAX. ;
 - WITHSTAND VOLTAGE: 500 VAC RMS
50 (60) Hz, 1MIN. ;
 - INSULATION RESISTANCE: 100MEGΩ MIN
@500V DC;
- MECHANICAL:
 - MATING FORCE: 44.1N MAX. ;
 - UNMATING FORCE: 9.8N MIN;
 - OPERATING LIFE: 10000 CYCLES MIN. ;
- ENVIRONMENTAL:
 - STORAGE TEMPERATURE RANGE: -40° C~+85° C;
 - OPERATION TEMPERATURE RANGE: -25° C~+70° C;
- SALT SPRAY TEST: 24H (Salt spray test 24hours for gold plated area and 8 hours for tin plated area)

3	外壳	铁	镀镍	
2	接触	铜	镀金	
1	基座	LCP	灰色	
序号	品 名	材 质	电镀/颜色	备 注

	深圳市虹成电子有限公司		品 名 TITLE	HDMI座	
			料 号 PART NO	HC-HDMI0019T-1A	
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1:1		
X.xxx ±0.10 X.xx ±0.20 X.x ±0.30		单 位 UNIT	MM	制 图 DRAW	AhYe
ANGULAR: X.xx' ±1' X.x' ±3' X.' ±5'		张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云
		版 本 REV	A	批 准 APPROVE	赵亮亮

