



# 产品承认书 SPECIFICATION FOR APPROVAL

客户名称:

CUSTOMER

我司料号:

OUR PART NO.

XRMW0707-2.5TBRG

我司品名:

OUR PART NAME

DIP Valiable Coils

送样日期:

DATE SAMPLES

数量:

QUANTITY

## 制造确认 MANUFACTURER APPROVE

拟制 DRAWN	审核 CHECKED	确认 APPROVED
HuFangting	RaoPin	Zhongcuilan

## 客户确认 CUSTOMER APPROVE

客户名称 CUSTOMER NAME:

客户料号 CUSTOMER P/N:

规格型号 DESCRIPTION:

XRMW0707-2.5TBRG

检查结果: ☐ 合格 ☐ 不合格

签名及盖章:

INSPECT RESULT ACCEPT REJECT

SIGNATURE AND STAMP

说明 REMARK:

如对本承认书内容有异议请提出或标记发送至我司, 本承认书在未收到异议回复时于本承认书提供一周后生效。

If you have any objection to the contents of this acknowledgement, please put forward or mark it and send it to our company. This acknowledgement will take effect one week after it is provided if you do not receive an objection reply.

东莞市祥如电子有限公司

Dongguan xiangru electronics co., ltd

Tel: 0769-86346548 Fax: 0769-86346358

Email: dgxiangru@126.com



## 修订记录 Revision record

[illegible]


## 产品承认书

### SPECIFICATION FOR APPROVAL

客户名称 CUSTOMER		日期 DATE	2025/9/10
客户物料编号 CUSTOMER P/N		客户规格型号 DESCRIPTION	XRMW0707-2.5TBRG
我司物料编号 OUR PART NO	XRMW0707-2.5TBRG	我司品名 OUR PART NAME	DIP Valiable Coils

外观尺寸 Appearance of size

单位 Unit: mm



A	6.6±0.2	C	9.3±0.2	E	5.0±0.1		
B	6.6±0.2	D	0.6±0.1	P	6.5±0.5		
标识Identification							

(以上尺寸为手工测量只做参考详细尺寸以实物为准)

应用范围	振荡	种类	可调电感	品牌	祥如 (XR)
型号	XRMW0707	封装形式	插件电感	绕线形式	单层间绕式
导磁体性质	铜芯 Copper core	磁芯形状	柱形 Columnar	工作频率	高频
安装方式	插件 plugin	骨架材料	工程塑料	品质因素Q	高频

XRMW   0707   -2.5T   B   R   G  
①                      ②                      ③                      ④                      ⑤                      ⑥

①Product Name: XRMW

②Dimensions: "0707" denotes a width of 6.6mm (Ref) and a height of 9.3mm (Ref).

③Coil Turns: "2.5T" indicates one and a half turns.

④Core Type: "A" represents aluminum core, "B" represents copper core, 'F' represents ferrite core, "AR" represents air core.

⑤

⑥Color: "G" denotes green.



产品承认书  
SPECIFICATION FOR APPROVAL

客户名称 CUSTOMER		日期 DATE	2025/9/10
客户物料编号 CUSTOMER P/N		客户规格型号 DESCRIPTION	XRMW0707-2.5TBRG
我司物料编号 OUR PART NO	XRMW0707-2.5TBRG	我司品名 OUR PART NAME	DIP Valiable Coils

电性参数 Electrical parameters					
产品型号 Part No.	电感中心值(nH) L(Nom)	最小电感值(nH) L(min)	最大电感值(nH) L(MAX)	Q值 (min)	测试频率(MHz) Test Freq
XRMW0707-2.5TBRG	28.3	23.4	33.2	40	100

特性及应用 (Features and Applications):

- pp可塑塑胶注模。  
PP plastic injection molding.
- 高稳定性，带外壳保护。  
High stability with protective housing.
- 电感值可以调整。  
Adjustable inductance value.
- 结构牢固，可上下两端任意调整。  
Robust construction with adjustable upper and lower ends.
- 频率范围：30MHzcw 250MHz。  
Frequency range: 30MHz cw to 250MHz.
- 温度系数：150±100ppm/℃ (Max)。  
Temperature coefficient: 150±100ppm/℃ (Max).
- 无线电设备、射频、振荡线圈。  
Radio equipment, RF, oscillation coils.
- 无线电调频、TV接收器、发射装置。  
Radio FM, TV receivers, transmitters.
- 汽车、无线通信、射频振荡电路应用。  
Automotive, wireless communication, RF oscillation circuit applications.

▲采用优质PP料加镀锡圆铜线制作的疏绕空芯线图压铸而成。  
Die-cast using high-quality PP material with tinned round copper wire to form loosely wound air-core wire



## 注意事项 Matters needing attention

1、本公司产品适用于 AV 设备、OA 设备、家电、信息服务等一般电子设备中。

Our products are designed and promoted for use in general electronic devices such as audio-video equipment, office automation equipment, home appliance and information service.

2、当本公司的产品使用在一般电子设备以外的领域时，对于此所引发的设备失效我司将不承担任何法律责任。

In case of using the product for the purpose other than general electronics devices, we shall not be held liable for any dysfunctions in or damage to the equipment with which the product is used.

3、本承认书只保证我司产品作为一个单体时的质量情况，当我司产品被安装到贵公司产品上时，请贵司对使用在贵司电路上的产品情况进行了有效评价和确认。

Our specification limits the quality of the component as a single unit. Please ensure the component is thoroughly evaluated in your application circuit.

4、不要对产品施加过大的振动或机械冲击；

Do not apply excessive vibration or mechanical shock to products.

5、为防止断线，请不要使用锋利的物体接触线圈，如镊子；

Do not touch wire with sharp objects such as tweezers to prevent wire breakage.

6、在产品贴装时不要使用过大的压力，避免磁芯断裂。

Do not apply excessive stress to products mounted on boards to prevent core breakage.

7、为保证端子电极的焊接特性和包装材料处于良好状态，请于本公司发货后 6 个月内使用本产品。同时，由于端子电极的焊接特性会随时间发生变化，如果贮存时间超过 6 个月，请首先确认其焊接特性后再安装使用。

To maintain the solderability of terminal electrodes and to keep the packing material in good condition, product should be used within 6 months from the time of delivery. And the solderability of products electrodes may decrease as time passes, so in case of storage over 6 months, solderability shall be checked before actual usage.

8、存放货物的仓库应满足以下条件 Store products in a warehouse in compliance with the following condition:

条件 Conditions	元件含包装物 Packing status	元件自身 Component itself
温度 Temperature	-25~+40℃	-25~+85℃
湿度 Humidity	30~70%RH	30~70%RH

9、不要使产品遭受温度和湿度的快速变化。

Do not subject products to rapid changes in temperature and humidity.

10、不要将产品存放在化学环境中，如硫酸气体或碱性气体中，否则会降低电极端子的焊接特性和使电感器腐蚀。

Do not store the products in chemical atmosphere such as one containing sulfurous acid gas or alkaline gas, that will causes poor solderability and corrosion of inductors.

11、为了避免受潮气、灰尘等物质的影响，产品应保管于货架上。

Store products on pallets to protect from humidity, dust, etc

12、产品应避免热冲击、振动以及直接光照等等。

Avoid heat shock, vibration, direct sunlight, etc.

