

PRODUCT NO.  
DSIC09LSGER








RoHS compliant

REV. ECN NO. DR DATE

NOTES :  
1.Specification:  
1>.Operating force:1000gf Max  
2>.Operating Temperature:-40° to+85°  
3>.Storage Temperature::-40° to+85°  
4>.Mechanical Life:3000cycles minimum  
5>.Electrical Life:2000cycles minimum  
2. PLATING:  
GOLD FLASH 1u"~2u" SOLDER TAIL,  
1u"~3u" GOLD PLATING ON THE CONTACT AREA,  
WITH 50u" NICKEL UNDERPLATING OVERALL.

3. PART NUMBER DESCRIPTION

DSIC XX L S G E R  
[包装方式: T=管装 R=Reel]  
[电镀层:E=接触部 1u"~3u" / 焊尾部 1u"~2u"]  
[G=镀金 S=内金外锡]  
[脚型: S脚 / J脚 / H脚 / A脚 / Z脚]  
[T=低推贴胶 S=低推不贴胶 L=长推]  
[产数: 02=2P ..... 08=8P 10=10P 12=12P]



| Number | Part Name        | Material     | Finished    |
|--------|------------------|--------------|-------------|
| ①      | Actuator         | UL94 V0      | White       |
| ②      | Cover            | UL94 V0      | Black       |
| ③      | Movable          | Copper Alloy | 1u"~3u"Gold |
| ④      | Terminal         | Brass        | 1u"~2u"Gold |
| ⑤      | Base             | UL94 V0      | Black       |
| ⑥      | Terminal Contact | Brass        | 1u"~3u"Gold |

| TOLERANCE UNLESS OTHERWISE SPECIFIED |           |
|--------------------------------------|-----------|
| LINER                                | ANGLES    |
| .0 ± 0.25                            | 0. ± 2°   |
| .00 ± 0.15                           | .0 ± 1°   |
| .000± 0.10                           | .00± 0.5° |
| DESIGN                               | kathy     |
| DRAWING                              |           |
| CHECK                                |           |
| APPRO.                               |           |

| INSPECTION |
|------------|
| COPY       |
| PROJECTION |
| 2012/04/12 |

|                                                      |                 |
|------------------------------------------------------|-----------------|
| 东莞市广普实业有限公司<br>DongGuan Kingtek Industrial Co., Ltd. |                 |
| TITLE<br>BY DSIC SERIES PITCH 2.54mm                 |                 |
| PRODUCT FAMILY DSIC SERIES                           |                 |
| PRAT NO. DSIC09LSGER                                 |                 |
| FILE NO. DSIC09LSGER-A                               |                 |
| SIZE<br>A4                                           | UNIT<br>mm      |
| SCALE<br>2 : 1                                       | SHEET<br>1 OF 1 |
| REV.<br>A                                            |                 |