








NOTES:


1. MATERIAL: HOUSING: HIGH TEMERATURE LCP, BLACK, UL 94 V-0 FLAME RETARDANT.
2. TERMINAL : COPPER ALLO
PLATING SPEC AS BELOW: CONTACT AREA PLATE NICKEL 1.25um MIN, PLATE Gold 0.76um MIN; SOLDER AREA PLATE NICKEL 1.25um MIN, PLATE MATT TIN 1.5~4.5um;
3. ELECTRICAL CHARACTERISTICS
CONTACT CURRENT RATING: 0.5A MPERE
VOLTAGE RATING: 30VAC
CONTACT RESISTACE: 50 MILLOHMS MAX
DIELECTRIC WITHSTANDING VOLTAGE: 300VD
4. ENVIRONMEENT
OPERATION TEMPERATURE: -40° C TO 85° C

TOLERANCE		UMax conn 东莞市友贸实业有限公司 DONGGUAN UMAX ENTERPRISE LIMITED		TITLE: QSFP28 CONNECTOR ASSEMBLY 38 POSITION					
LINEAR	ANGLES			PART NO. UMAX952L0301					
X,±0.40	X°,± 3°			DWG NO. C-UMAX952L					
.X±0.30	.X°± 2°	APPD: Jason	MAT'L:			UNITS	SCALE	SHEET	REV
.XX±0.20	.XX°± 1°	CHKD: Schumi	FINISH:						
.XXX±0.10	.XXX°± 0.5°	DRWN:Lei Songping	Q'TY:						



REV	ECN NO.	NAME	DATE





PCB LAYOUT
PCB TOLERANCE ±0.05



DETAIL B(SCALE 2:1)



QSF28 MOUDLE CARD



DETAIL A(SCALE 2:1)

TOLERANCE		UMax conn 东莞市友贸实业有限公司 DONGGUAN UMAX ENTERPRISE LIMITED		TITLE: QSF28 CONNECTOR ASSEMBLY 38 POSITION				
LINEAR	ANGLES			PART NO. UMAX952L0301				
X±0.40	X°± 3°			DWG NO. C-UMAX952L				
.X±0.30	.X°± 2°	APPD: Jason	MAT'L:		UNITS	SCALE	SHEET	REV
.XX±0.20	.XX°± 1°	CHKD: Schumi	FINISH:		MM	1 : 1	2 OF 2	A0
.XXX±0.10	.XXX°± 0.5°	DRWN:Lei Songping	Q'TY:					