



3. Electrical
3.1 Rated Current & Voltage: DC12V, 1.0A
3.2 Contact Resistance: 100mΩ Max. at working height
4. Operational Temperature: -40°C ~ +85°C
5. Mechanical
Force: 30±5g, at working height
Durability: 10000 cycles
6. 12H delay test



5.0				DRAWING: Frank	GENERAL TOLERANCE .X:=±0.30 .X°:=±2° .XX:=±0.20 .XX°:=±1° .XXX:=±0.10 .XXX°:=±0.5°		CHIN-BAN Electroic Technology	
4.0								
3.0				CHECKED: yang jie	UNIT: MM	PROJECTION:	DESCRIPTION: POGOpin Connector	
2.0								
1.0				APPROVAL:	SCALE: 1/1		SERIES: PG1000 SERIES	REV: 1.0
REV.	DATE	DESCRIPTION	DRAWING		SHEET: 1/1		PART NO: PG1000-01-010P	CUSTOMER P/N: