

SOT-23 Plastic-Encapsulate Transistors



Features

- Built-in bias resistors enable the configuration of an inverter circuit without connecting external input resistors(see equivalent circuit)
- The bias resistors consist of thin-film resistors with complete isolation to allow positive biasing of the input.They also have the advantage of almost completely eliminating parasitic effects
- Only the on/off conditions need to be set for operation, making device design easy


Mechanical Data

- Case: SOT-23
Molding compound meets UL 94V-0 flammability rating, RoHS-compliant, halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750,Method 2026

Function Diagram



Supply Voltage
VCC 50V
Collector Current
0.07 Ampere



Ordering Information

Table with 7 columns: PACKAGE, PACKAGE CODE, UNIT WEIGHT(g), REEL(pcs), BOX(pcs), CARTON(pcs), DELIVERY MODE. Row 1: SOT-23, R1, 0.0085, 3000, 15000, 150000, 7"

Maximum Ratings (Ta=25°C Unless otherwise specified)

Table with 4 columns: PARAMETER, SYMBOL, UNIT, VALUE. Rows include Supply Voltage (VCC, V, 50), Input Voltage (VIN, V, -6~+40), Output Current (IO, mA, 70), Power Dissipation (PD, mW, 200), Storage temperature (Tstg, °C, -55 ~+150), and Junction temperature (Tj, °C, -55 ~+150).





Small-signal Characteristics

Table with 7 columns: ITEM, SYMBOL, Condition, UNIT, Min, Typ, Max. Row 1: Transition frequency, fT, IO= 5mA, VO= 10V, MHz, -, 250, -

Electrical Characteristics (Ta=25°C Unless otherwise noted)

PARAMETER	SYMBOL	UNIT	Condition	Min	Typ	Max
Input voltage	$V_{I(off)}$	V	$I_o=100\mu A, V_{cc}=5V$	0.3	-	-
	$V_{I(on)}$		$I_o=1mA, V_o=0.3V$	-	-	1.4
Output voltage	$V_{O(on)}$		$I_o/I_i=5mA/0.25mA$	-	-	0.3
Input current	I_i	mA	$V_i=5V$	-		0.88
Output current	$I_{O(off)}$	μA	$V_{cc}=50V, V_i=0V$	-	-	0.5
DC Current Gain	G_i	-	$V_o=5V, I_o=5mA$	68	-	-
Input resistance	R_i	k Ω	-	7	10	13
Resistance ratio	R_2/R_1	-	-	3.7	4.7	5.7

Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)



● Package Outline Dimensions (SOT-23)

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	0.90	1.15	0.035	0.045
A1	-	0.10	-	0.004
A2	0.90	1.05	0.035	0.041
b	0.30	0.50	0.012	0.020
c	0.10	0.20	0.004	0.008
D	2.80	3.00	0.110	0.118
E	1.20	1.40	0.047	0.055
E1	2.25	2.55	0.089	0.100
e	0.950TYP		0.037TYP	
e1	1.80	2.00	0.071	0.079
L	0.550REF		0.022REF	
L1	0.30	0.50	0.012	0.020
θ	-	8°	-	8°

● Suggested Pad Layout

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
J	0.80	-	0.031	-
K	-	0.90	-	0.035
M	2.00	-	0.078	-
N	-	1.90	-	0.074