






RoHS

* 针头歪斜度3°



PCB LAYOUT

Notes:

1.Materials:

- 1.1 Plunger:Brass C3604
- 1.2 Barrel: Brass C3604
- 1.3 Spring: SUS304

2.Plating:

- 2.1 Plunger: 5u" Au over 50-120u" Ni
- 2.2 Barrel: 5u" Au over 50-120u" Ni

3.Electrical

- 3.1 Rated Current&Voltage: DC12V,2.0A
 - 3.2 Contact Resistance: 100mΩ Max. at working height
- 4.Operational Temperature: -40°C~+85°C
- 5.Mechanical

- Durability:5000 cycles
- 6. 24H delay test

5.0				DRAWING:	GENERAL TOLERANCE .X:=±0.30 .X':=±2° .XX:=±0.20 .XX':=±1° .XXX:=±0.10 .XXX':=±0.5°		CHIN-BAN Electroic Technology	
4.0				Frank				
3.0				CHECKED:	UNIT: MM	PROJECTION:	DESCRIPTION: POGO pin Connector	
2.0				yang jie	SCALE: 1/1		SERIES: PG1000 SERIES	REV: 1.0
1.0				APPROVAL:	SHEET: 1/1		PART NO: PG1000-01-014P	SIZE: A4
REV.	DATE	DESCRIPTION	DRAWING				CUSTOMER P/N:	