CMB200N06-7

60V, 1.7mΩ typ., 180A N-Channel MOSFET

General Description

The CMB200N06-7 is N-channel MOS Field Effect Transistor designed for high current switching applications.


Product Summary


BVDSS	$R_{DS(on)}$ max.	ID
60V	2.1mΩ	180A

Applications

- Switching application

TO-263-7 Pin Configuration





Type	Package	Marking
CMB200N06-7	TO-263-7	CMB200N06-7

Features

- Low On-Resistance
- 100% avalanche tested
- RoHS Compliant

Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	60	V
V_{GS}	Gate-Source Voltage	±20	V
I_D@T_C=25℃	Continuous Drain Current	180	A
I_D@T_C=100℃	Continuous Drain Current	125	A
I_{DM}	Pulsed Drain Current	720	A
EAS	Single Pulse Avalanche Energy[1]	7290	mJ
P_D@T_C=25℃	Total Power Dissipation	330	W
T_{STG}	Storage Temperature Range	-55 to 150	℃
T_J	Operating Junction Temperature Range	-55 to 150	℃

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JA}$	Thermal Resistance Junction-ambient (min. footprint)	---	91	℃/W
$R_{\theta JC}$	Thermal Resistance Junction-case	---	0.38	℃/W

Electrical Characteristics(T_J=25℃, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	V_{GS}=0V , I_D=250uA	60	---	---	V
$R_{DS(ON)}$	Static Drain-Source On-Resistance	V_{GS}=10V , I_D=80A	---	1.7	2.1	mΩ
$V_{GS(th)}$	Gate Threshold Voltage	V_{GS}=V_{DS} , I_D =250uA	2.0	---	4.0	V
I_{DSS}	Drain-Source Leakage Current	V_{DS}=60V , V_{GS} =0V	---	---	1	μA
I_{GSS}	Gate-Source Leakage Current	V_{GS} =±20V , V_{DS}=0V	---	---	±100	nA
gfs	Forward Transconductance	V_{DS}=10V , I_D=20A	---	54	---	S
R_g	Gate Resistance	V_{DS}=0V , V_{GS}=0V , f=1MHz	---	1.2	---	Ω
Q_g	Total Gate Charge	I_D=80A V_{DD}=30V V_{GS}=10V	---	183	---	nC
Q_{gs}	Gate-Source Charge		---	45	---	
Q_{gd}	Gate-Drain Charge		---	75	---	
$T_{d(on)}$	Turn-On Delay Time	V_{DD}=30V V_{GS} =10V R_{G_ext} =3Ω I_D =80A	---	31	---	ns
T_r	Rise Time		---	118	---	
$T_{d(off)}$	Turn-Off Delay Time		---	71	---	
T_f	Fall Time		---	149	---	
C_{iss}	Input Capacitance	V_{DS}=25V , V_{GS}=0V , f=1MHz	---	8100	---	pF
C_{oss}	Output Capacitance		---	1400	---	
C_{rss}	Reverse Transfer Capacitance		---	1000	---	

Diode Characteristics


Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_S	Continuous Source Current	V_G=V_D=0V , Force Current	---	---	180	A
I_{SM}	Pulsed Source Current		---	---	720	A
V_{SD}	Diode Forward Voltage	V_{GS}=0V , I_S=80A ,T_J=25℃	---	0.83	1.2	V

Note :


1.The EAS data shows Max. rating . The test condition is V_{DD}=50V , V_{GS}=10V , L=5mH , I_{AS}=54A.

This product has been designed and qualified for the counsumer market.
Cmos assumes no liability for customers' product design or applications.
Cmos reserver the right to improve product design ,functions and reliability wihtout notice.Please refer to the latest version of specification.


Typical Characteristics




Output Characteristics




transfer characteristics




On-Resistance vs. Drain Current



Gate charge vs gate-source voltage




Capacitance Characteristics



Body-Diode Characteristics

Package Dimension

TO-263-7 Unit :mm



SYMBOL	mm			SYMBOL	mm		
	MIN	NOM	MAX		MIN	NOM	MAX
✻A	4.30	4.40	4.50	E1	8.20	8.40	8.60
✻A1	0.00	0.10	0.20	✻e	1.25	1.27	1.29
✻A2	1.22	1.27	1.32	✻H	14.85	15.00	15.15
✻A3	2.30	2.40	2.50	H1	1.10	1.20	1.30
✻b	0.50	0.60	0.70	✻L	4.50	4.70	4.90
✻b1	-	-	0.63	L1	1.70	2.00	2.30
✻c	0.45	0.50	0.55	L2	4.55	4.65	4.75
✻D	9.15	9.30	9.45	S	1.40	1.50	1.60
D1	规格A：8.00REF			Q	2.80	2.90	3.00
	规格B：5.70REF			✻θ	0°	2.5°	8°
✻E	10.12	10.16	10.20	θ1	5°	7°	9°