




RECOMMEND PULG



PCB. WELDING DRAWING (TOLERANCE: ± 0.05)

GENERAL TOLERANCES
UNLESS SPECIFIED

<i>PIN</i>	<i>MODLE</i>
$\emptyset 1.0$	<i>DC047-A10</i>
$\emptyset 1.3$	<i>DC047-A13</i>

2	TIP SPRING	1	PHOSPHOR BRONZE	MB:CuSn PLATED	
1	CENTER PIN	1	BRASS	MB:CuSn PLATED	
LTR	PART NAME	QTY	MATERIAL	REMARK	
GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司  Shenzhen Huamingtong Electronics Co., Ltd			
X.* ±0.30	X.* ±5°	PART NO.		TITLE:	
X.X* ±0.25	X.X* ±1°	DC047-AN		DC SOCKET	
X.XX* ±0.15		DESIGN: James	CUSTOMER	SIZE	
MANUFACTURE DWG		CHED: Talen		A4	UNITS
		APPD: Sophia		SCALE	SHEET
				N:A	
				1/1	



HMT CONN

深圳市华明通电子有限公司

Shenzhen Huamingtong Electronics Co., Ltd

X.° ±0.30	X.° ±5°
X.X° ±0.25	X.X° ±1°
X.XX° ±0.15	

0	X°	$\pm 5^\circ$
5	X°	$\pm 1^\circ$

•	PART NO.
•	DC047-AN

TITLE: *DC SOCKET*

DESIGN:	James
CHED:	Talen
APPD:	Sophia

CUSTOMER	SIZE	UNITS
	A4	MM
	SCALE	SHEET
	N:A	1/1