







REV	LTR	DESCRIPTION	DATE	APPROVED
A0		依新料号编码原则发行图面		



PIN	SIGNAL NAME
B12	GND
B9	VBUS
B5	CC2
A5	CC1
A9	VBUS
A12	GND

H	H	=0.9
H	H	=1.5

规格说明 Specifications:

1. 电气特性 Electrical:

额定电压(Rated voltage): 5V DC

额定电流(Rated current): 3A VBUS引脚;

1.25A用于GND引脚, 其他引脚为0.25A.

接触电阻(Contact resistance): 40mΩ Max

测试条件:20mv, 100mA下测量.

绝缘电阻(Insulation resistance): 100MΩ Min

耐电压(Withstand Voltage): 100V AC

2. 机械性能 Mechanical:

插入力(Mate force): 0.5-2.0Kg

拔出力(Unmate force): 0.6-2.0Kg

插拔次数(Durability): 5000 Cycles.

3. 材料 Material:

胶芯(Housing): LCP UL94 V-0

端子(Contact): C2680, T=0.2mm; 镍底, 镀金

外壳(Shell): 不锈钢201-H 表面镀镍

4. 温度范围(Temperature Range): -30℃ to +80℃.

TOLERANCE	NAME(INTENDED USE) CUSTOMER DRAWING	深圳市韩下电子有限公司
X.X ±0.30 X.* ±10*	PART NO.	TITLE: TYPE-C
.XX ±0.20 X.* ± 8*	HX TYPE-C 6P LT H10.0	DESIGN: 黄 彬 2020.5.26
.XXX ±0.10 .XX* ± 5*	UNITS mm	CHED: 张 伟 2020.5.26
MATERILA	APPD: 罗小春 2020.5.26	DRAWG NO
FINISH		SCALE SHEET REV.