




规格说明: Specifications:

电气特性: Electrical:

1. 额定电流: Current Rating
1A/contact terminal
2. 额定电压: Voltage Rating
30V DC
3. 接触阻抗: Contact Resistance
30 milliohms MAX
4. 耐电压: Dielectric Withstanding Voltage
500 V AC AT Sea Level
5. 绝缘阻抗: Insulation Resistance
1000MEGA ohms MIN

物理性能: Mechanical:

1. 插拔力: Connector Mate and Unmate Force
Mate force: 35N (MAX)
Unmate force: 7N (MIN)

材料: Material:

1. 塑胶: Housing:
PBT
2. 端子: Contact:
Copper Alloy C2680
3. 外壳: Shell:
SPCC

电镀Finish:

1. 端子: Contact:
Plated Gold in Mating Area,
Tin On Solder Tails
2. 外壳: Shell:
Nickel Plating

温度范围: Temperature Range:
-30°C to +80°C

TOLERANCE UNLESS OTHERWISE SPECIFIED	
.XXX	±0.10
.XX	±0.25
.X	±0.35
.X'	±3°

产品名称

PART NAME:

USB AF

料号

PART NO:

HX AF 10.0 180° JB-HJ

C

PROJECTION:



THIRD ANGLE PROJECTION

CHECKED

张伟

UNIT:

SCALE

REV(NO)

SHEET

DRAWN

黄彬

mm

1:1

A

1 OF 1

DATE

2011.12.05



深圳市韩下电子有限公司