





项 目	变 更 内 容	日 期	修 改 人	核 准
Mapx	Modification	Date	Draw	Approve



RECOMMENDED P.C.B LAYOUT

规格说明: Specifications:

电气特性: Electrical:

1. 额定电流: Current Rating
1A/contact terminal
2. 额定电压: Voltage Rating
30V DC
3. 接触阻抗: Contact Resistance
30 milliohms MAX
4. 耐电压: Dielectric Withstanding
Voitage

500 V AC AT Sea Level

5. 绝缘阻抗: Insulation Resistance
1000MEGA ohms MIN

物理性能: Mechanical:

1. 插拔力: Connector Mate and Unmate Force
Mate force: 35N (MAX)
Unmate force: 7N (MIN)

材料: Material:

1. 塑胶: Housing:
PBT
2. 端子: Contact:
Copper Alloy C2680
3. 外壳: Shell:
SPCC

电镀Finish:

1. 端子: Contact:
Plated Gold in Mating Area,
Tin On Solder Tails
2. 外壳: Shell:
Nickel Plating

温度范围: Temperature Range:
-30°C to +80°C

成品图 MANUFACTURE DWG		深圳市韩下电子有限公司									
公差一览表 TOLERANCE UNLESS OTHERWISE											
.X±0.20	X.±5'	日期 DATE	2016.10.20	单位 UNIT	MM	制图 DRAWING	黄彬	DWG NO.			
.XX±0.10	.X±2'	审核 CHECKED	张伟	比例 SCALE	1 : 1	品名 NAME	HX 10.0 HC6.3 JB				
.XXX±0.05	.XX±1'	核准 APPROVE	罗小春	画法 VIEW			版本 VER.	AO	页 数 SHEET	003	