



REV.	ECN NO.	REVISED	DATE

NOTE:
1.MATERIAL:
a.HOUSING:PPA BLACK
b.CONTACT:PHOSPHOR BRONZE
(SURFACE PLATING: Au1u")
SEE ORDERING INFORMATION

2.ELECTRIC:
a.CONTACT RESISTANCE: 30 MILLIOHMS MAX
b.INSULATION RESISTANCE: 100 MEGA OHMS MIN
c.DIELECTNIC VOLTAGE: 500V AC ONE MINUTE
d.OPERATING TEMPERATURE: -25° C~ +85° C







ORDERING INFORMATION
BS-08-B2BA021

电池座系列
BS-08系列
SMT 180° TYPE

PLATING:
A-Au1U"
J-Ni100U"~120U"
K-Sn100U"~120U"

MATERIAL:
1A-PBT BLACK
1B-PA66 BLACK
2A-PPA BROWN
2B-PPA BLACK
3A-PPS BROWN
3B-PPS BLACK
4A-LCP WHITE
4B-LCP BLACK

工程部
2023-11-29
LQ. HUANG



PCB Layout Diagram
Top View

3	TERMINAL(-)	1	PHOSPHOR BRONZE, T=0.20mm	Gold Plating and Ni Under-Plating
2	TERMINAL(+)	1	PHOSPHOR BRONZE, T=0.20mm	Gold Plating and Ni Under-Plating
1	HOUSING	1	PPA	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美用 www.meiyoungdz.com			
DECIMALS:	ANGLES:	DSND	Huanglieqing	DATE	2023-11-29
X :±0.30	X :±1°	CHKD	ZhouRuicai	DATE	2023-11-29
X.X :±0.25	X.X :±0.5°	APVD	XueShunyang	DATE	2023-11-29
X.XX :±0.20		WEIGHT:	9	SCALE:	SIZE: A4
X.XXX :±0.10		SHEET 1 OF 1		VIEW:	UNIT: mm
				REV.: A/0	OBJECT: MY
				DRAW NO.:MY-CP-0079	

TITLE:
BS-2032-8KZ 5MM SMT
PART NO.:
BS-08-B2BA021