

BCBF170N650T1

N-Channel Silicon Carbide Power MOSFET

1700 V, 8 A , 650 mΩ




Features

- High blocking voltage
- Low on-resistance with high junction temperature
- High-speed switching with low capacitances
- Fast intrinsic diode with low reverse recovery (Qrr)

$BV_{DSS}, T_c=25^{\circ}C$	$I_D, T_c=25^{\circ}C$	$R_{DS(on),typ}$	$Q_{g,typ}$
1700 V	8A	650 mΩ	13.2 nC

Benefits

- Higher System Efficiency
- Reduce cooling requirements
- Increased power density
- Enabling higher frequency
- Minimize gate ringing



Applications

- DC/DC converters
- Solar Inverters
- Battery Chargers
- Motor Drives
- Auxiliary power supply



Absolute Maximum Ratings (T_J = 25°C unless otherwise noted)

Symbol	Parameter		Value	Unit
V _{DSS}	Drain to Source Voltage		1700	V
V _{GSmax}	Gate to Source Voltage (AC f> 1Hz)		-10 / +25	V
V _{GSop}	Recommended Operation Value		-5 / +20	V
I _D	Drain Current	V _{GS} =15V, (T _C = 25°C)	8	A
		V _{GS} =15V, (T _C = 100°C)	6	
		V _{GS} =20V, (T _C = 25°C)	8.6	
I _{DM}	Drain Current	Pulsed (Note1)	17	A
P _D	Power Dissipation (T _C = 25°C)		78	W
T _J , T _{STG}	Operating and Storage Temperature Range		-55 to 175	°C

※Note 1 : Limited by maximum junction temperature.

Thermal Characteristics

Symbol	Parameter	Value	Unit
R _{θJC}	Thermal Resistance, Junction to Case, Max.	1.92	°C/W
T _{sold}	Soldering temperature, wave soldering only allowed at leads	260	°C

Electrical Characteristics ($T_J = 25^\circ\text{C}$ unless otherwise noted)

Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit
--------	-----------	-----------------	-----	-----	-----	------

Off Characteristics

BV_{DSS}	Drain to Source Breakdown Voltage	$V_{GS} = 0\text{ V}, I_D = 100\text{ }\mu\text{A}$	1700	-	-	V
I_{DSS}	Zero Gate Voltage Drain Current	$V_{DS} = 1700\text{ V}, V_{GS} = 0\text{ V}$	-	0.9	100	μA
I_{GSS}	Gate-Source Leakage Current	$V_{GS} = +20\text{ V}$	-	2	250	nA

On Characteristics

$V_{GS(th)}$	Gate Threshold Voltage	$V_{GS} = V_{DS}, I_D = 0.5\text{ mA}$	1.8	2.8	4.0	V
$R_{DS(on)}$	Static Drain to Source On Resistance	$V_{GS} = 20\text{ V}, I_D = 2\text{ A}$	-	550	1000	mΩ
		$V_{GS} = 18\text{ V}, I_D = 2\text{ A}$	-	650	-	
		$V_{DS} = 15\text{ V}, I_D = 2\text{ A}$	-	750	-	

Dynamic Characteristics

C_{iss}	Input Capacitance	$V_{GS} = 0\text{ V}, V_{DS} = 1000\text{ V}$ $f = 1.0\text{ MHz}, V_{AC} = 25\text{ mV}$	-	183	-	pF
C_{oss}	Output Capacitance		-	17.1	-	
C_{rss}	Reverse Capacitance		-	2.1	-	
E_{oss}	Stored Energy in Output Capacitance		-	10.1	-	μJ
$Q_{g(tot)}$	Total Gate Charge	$V_{DS} = 1200\text{ V}, I_D = 2\text{ A}$ $V_{GS} = -5\text{ V} / +20\text{ V}$	-	13.2	-	nC
Q_{gs}	Gate to Source Charge		-	5.0	-	
Q_{gd}	Gate to Drain "Miller" Charge		-	4.5	-	
R_G	Internal Gate Resistance	$f = 1.0\text{ MHz}, V_{AC} = 25\text{ mV}$ open drain	-	25.2	-	Ω







Switching Characteristics

$t_{d(on)}$	Turn-On Delay Time	$V_{DS} = 1000\text{ V}$ $I_D = 2\text{ A}$ $V_{GS} = -5\text{ V} / +20\text{ V}$ $R_{G(ext)} = 2.5\text{ }\Omega$ $L = 70\text{ mH}$	-	5	-	ns
t_r	Turn-On Rise Time		-	17	-	
$t_{d(off)}$	Turn-Off Delay Time		-	13	-	
t_f	Turn-Off Fall Time		-	55.6	-	
E_{on}	Turn-on Switching Energy		-	170	-	μJ
E_{off}	Turn-off Switching Energy		-	68	-	







Source-Drain Diode Characteristics

I_S	Maximum Continuous Diode Forward Current		-	-	8	A
V_{SD}	Diode Forward Voltage	$V_{GS} = 0\text{ V}, I_S = 1\text{ A}$	-	4.0	-	V
I_{rm}	Peak Reverse Recovery Current	$V_{DS} = 1200\text{ V}, I_S = 2\text{ A},$ $V_{GS} = -5\text{ V}, \text{dif/dt} = 1200\text{ A}/\mu\text{s}$	-	3	-	A
t_{rr}	Reverse Recovery Time		-	33	-	ns
Q_{rr}	Reverse Recovery Charge		-	32	-	nC







Typical Performance Characteristics









Typical Performance Characteristics





Typical Performance Characteristics




Typical Performance Characteristics



Typical Performance Characteristics



Package Outlines
TO263-7



* Dimensions in millimeters

Package Marking and Ordering Information

Part Number	Top Marking	Package	Packing Method	Quantity
BCBF170N650T1	BCBF170N650T1	TO263-7	Tape & Reel	800 units

Disclaimer

Bestirpower reserve the right to make changes, corrections, enhancements, modifications, and improvements to Bestirpower products and/or to this document at any time without notice.

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. Bestirpower does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Products or technical information described in this document.

This document is the property of Bestirpower Co., LTD., and not allowed to copy or transformed to other format if not under the authority approval.

© 2024 bestirpower – All rights reserved