

*MESSRS.*SPECIFICATION FOR APPROVAL
承 認 书

Product	DYNAMIC SPEAKER
Part No.	HDK-241508AA-3C5 (RoHS)
Customer	
Customer Part No.	

Approved By	Checked By	Made By
王台平 STEP-23-2022	曹丽萍 STEP-23-2022	LILY STEP-23-2022

常州华龙电子有限公司

Changzhou Dragon State Electronic Co., Ltd

中国江苏省常州市新区电子园新四路 36 号

Tel: +86-519-85110078. 86-519-85106698, Fax: +86-519-85101081

EDITION:1.1

1. Specification

HDK-241508AA-3C5 (RoHS)

ITEM		SPECIFICATIONS	
01	Type	Dynamic speaker	
02	Dimension	External diameter 24×15 mm	
03	Rated Input Power	1.0W	
04	Max. Input Power	1.3W for 1 minute	
05	Impedance	8 ohm $\pm$ 15% at 2000Hz 1.0V	
06	Resonance Frequency (Fo)	950Hz $\pm$ 20% at Fo 1V	
07	Sensitivity (S.P.L.)	90dB (0.1W / 0.1m) $\pm$ 3 dB	at AVE 1.0K, 2K, 3K, 4K, 5KHz.
08	Frequency Range	Fo - 10KHz	
09	Total Harmonics Distortion	Max 5 % at 2KHz, 1.0W.	
10	Weight	2.7g $\pm$ 0.2g	
11	Appearance	Should not exist any obstacle to be harmful to normal operation; damages, cracks, rusts and distortions, etc.	
12	Operation Test	Must be normal at program source - 1.0W	
13	Buzz, Rattle, etc.	Should not be audible at 2.83V sine Wave between 300 to 5KHz	
14	Polarity	When positive voltage is applied to the terminal marked (+), diaphragm should move to the front.	
15	Terminal Strength	Capable of withstand 1kg load for 30 seconds without resulting in any damage or rejection.	
16	Temperature	Operating temperature: -20℃ to +60℃ Storage temperature: -30℃ to +70℃	

2-1. Test Condition

Standard

Temperature : 15 ~ 35℃

Relative humidity : 25% ~ 85%,

Atmospheric pressure : 860mbar to 1060mbar.

Basic

Temperature : 20±3℃

Relative humidity : 60% ~ 70%,

Atmospheric pressure : 860mbar to 1060mbar

2-2. Standard Test Fixture


1. Input Power : 0.1W (0.89V)

2. Zero Level : -dB


3. Mode : SPEAKER

4. potentiometer Range : 50dB


5. Sweep Time : 0.5sec




2-3. Frequency Response Curve



3. Dimension






4. Reliability Test

Items.		Specifications
01	High temp. Test	Keep 96 hours at $+70^{\circ}\text{C} \pm 3^{\circ}\text{C}$ and leave 3 hours in normal temperature and then check
02	Low temp. Test	Keep 96 hours at $-30^{\circ}\text{C} \pm 3^{\circ}\text{C}$ and leave 3 hours in normal temperature and then check
03	Humidity test	Keep 96 hours at $+40^{\circ}\text{C} \pm 3^{\circ}\text{C}$ relative humidity 95% and leave 3 hours in normal temperature and then checked.
04	Temp./Humidity cycle	The part shall be subjected 5 cycles. One cycle shall be 12 hours and consist of; 
05	Thermal cycle test.	Low temperature: $-30^{\circ}\text{C} \pm 3^{\circ}\text{C}$, temperature: $+70^{\circ}\text{C} \pm 3^{\circ}\text{C}$, cycle: 1 hour/cycle each, and then keep 5 cycles in a room.
06	Vibration	10~200~10Hz sin-wave sweep 15min. 5G(constant) X, Y, Z 3 direction. 2 hours each, total 6 hours.
07	Fix drop test	Fix on jig. Then drop from 152cm height to the concrete floor X, y, z 6 direction. 5 times each, total 30 times.
08	Free drop test	Free drop from 100cm height to the concrete floor X, y, z 6 direction. 1 times each, total 6 times.
09	Rated Power test	Rated Power white noise is applied for 96 hours
10	Max Power test	Max power 1 min on - 2 min off 10 cycles.
11	Terminal strength test	Capable of withstand 1kg load for 30 seconds without resulting in any damage or rejection.
Criterion: After these test , the change of S.P.L shall be within ± 3 dB .		

Soldering Condition

Recommend using constant branding iron in 15 ~ 30W, and in temperature range $350 \pm 10^{\circ}\text{C}$. Soldering time not over 3 seconds.

5. Packing

REV NO.	REVISION NOTE	APPROVAL	DATE
			
	Cover(320*220*5mm) Material: Eps		
	↓		
			
	Box(320*220*13.5mm) 100pcs Material: Eps		
	↓		
			
	Middle(320*220*140mm) 1000pcs Material: Eps		
	↓		
			
	Outer Box(360*270*280mm) 2000pcs Material: Paper		
单位: mm			
TITLE: packing		DRAWN: Lily 2015/4/23	
PART NO.		DESIGNED: R&D OF D.S.	
		CHECKED: Emily	
DWG NO.		APPROVAL: Eric	
		MATERIAL: ***	
1 REV		SCALE: 2:1	
		SHEET: 1 of 1	
		UNITS: mm	
		TOLERANCE	
		20~11	± 0.3
		10~5	± 0.2
		<4	± 0.1
DS Changzhou Dragon State Electronic Co., Ltd			