



| REV. | ECN NO. | REVISED | DATE |
|------|---------|---------|------|
|      |         |         |      |

NOTE:

1.MATERIAL:

- a.HOUSING:LCP WHITE  
b.CONTACT:PHOSPHOR BRONZE  
(SURFACE PLATING:Ni100u"-120u")

SEE ORDERING INFORMATION

2.ELECTRIC:

- a.CONTACT RESISTANCE: 100 MILLIOHMS MAX  
b.INSULATION RESISTANCE: 100 MEGA OHMS MIN  
c.DIELECTNIC VOLTAGE: 500V AC FOR ONE MINUTE  
d.OPERATING TEMPERATURE: -25°C~ +85°C

ORDERING INFORMATION

BS-06-A4AJ022

电池座系列

BS-06系列

DIP 90° TYPE





PLATING:  
A-Au1U"  
J-Ni100U"~120U"  
K-SN100U"~120U"

MATERIAL:  
1A-PBT BLACK  
1B-PA66 BLACK  
2A-PPA BROWN  
2B-PPA BLACK  
3A-PPS BROWN  
3B-PPS BLACK  
4A-LCP WHITE  
4B-LCP BLACK

工程部

2023-05-15

LQ. HUANG



PCB Layout Diagram  
Top View

|     |             |      |                |                         |
|-----|-------------|------|----------------|-------------------------|
| 3   | TERMINAL(-) | 1    | C5191 T=0.20MM | Ni(100u"-120u")-Plating |
| 2   | TERMINAL(+) | 1    | C5191 T=0.20MM | Ni(100u"-120u")-Plating |
| 1   | HOUSING     | 1    | LCP            | WHITE                   |
| NO. | PART NAME   | Q'TY | MATERIAL       | PLATING & COLOR         |

|                                                                    |  |                                 |  |             |              |                                                                                             |            |                          |  |
|--------------------------------------------------------------------|--|---------------------------------|--|-------------|--------------|---------------------------------------------------------------------------------------------|------------|--------------------------|--|
| UNLESS OTHERWISE<br>SPECIFIED TOLERANCES                           |  | MYOUNG 美阳 www.meiyangdz.com     |  |             |              |                                                                                             |            |                          |  |
| DECIMALS:<br>X :±0.30<br>X.X :±0.25<br>X.XX :±0.20<br>X.XXX :±0.10 |  | ANGLES:<br>X :±1°<br>X.X :±0.5° |  | DSND        | Lieqinghuang | DATE                                                                                        | 2023-05-15 | TITLE:                   |  |
|                                                                    |  | CHKD                            |  | ZhouRuicai  |              | DATE                                                                                        | 2023-05-15 | BS-2032-6-2 Ni DIP LCP白色 |  |
|                                                                    |  | APVD                            |  | XueShunyang |              | DATE                                                                                        | 2023-05-15 | PART NO.:                |  |
| WEIGHT: 9                                                          |  | SCALE:                          |  | SIZE: A4    |              | VIEW:  |            | BS-06-A4AJ022            |  |
| SHEET 1 OF 1                                                       |  | UNIT: mm                        |  | REV.: A/0   |              | OBJECT: MY                                                                                  |            | DRAW NO.:MY-CP-0168      |  |