

TMI8140 40V 7A H-Bridge DC Motor Driver

FEATURES

- H-Bridge DC Motor Driver
- 6.8-V to 40-V Operating Supply Voltage Range
- Low Power Standby Mode
- High Output Current Capability
 - DFN6X5_15L: 7-A DC, 10-A Peak
- PWM Control Interface
- $R_{ds(on)}(HS+LS)$: 45~50 m Ω
- Protection Features
 - VCC Undervoltage Lockout (UVLO)
 - Overcurrent Protection (OCP)
 - Thermal Shutdown (TSD)
 - Integrated Fast Stop Function
- Package and Footprint:
 - DFN6X5_15L

APPLICATIONS

- Electronic locks
- Electric toys
- Massager
- Robots

TYPICAL APPLICATION




Figure 1. Basic Application Circuit

GENERAL DESCRIPTION

The TMI8140 is a DC bidirectional motor driver, suitable for medium and large current motors.

The two logic input terminals(IN1/IN2) are used as the input of PWM control mode to control the direction of current flow through the H-bridge, and hence the direction of rotation of a DC motor.


This circuit has good anti-interference, tiny standby current, ultra-low output internal resistance, using BCD process, strong withstand voltage, and strong reverse surge current capability to release inductive load.

The package form of TMI8140 is DFN6X5_15L, and is comply with ROHS specifications, and the lead frame is 100% lead-free.

ABSOLUTE MAXIMUM RATINGS (Note 1)

Parameter	Value	Unit
Power supply voltage (VCC)	-0.3~40	V
Logic input voltage (IN2, IN1)	-0.3~VCC	V
Output continuous current (IOOUT) (DFN6X5_15L)(Note 2)	0~7.0	A
Operating ambient temperature	-40~125	°C
Power consumption (PD)	2.5	W
Operating junction temperature (Note 3)	-40~150	°C
Storage temperature	-55~150	°C

PACKAGE/ORDER INFORMATION



TMI8140 (Top View)
DFN6X5_15L

Part Number	Package	Top mark	Quantity/ Reel
TMI8140	DFN6X5_15L	TMI8140 XXXXXX	5000

TMI8140 device is Pb-free and RoHS compliant.

PIN FUNCTIONS

Pin	Name	I/O	Description
1、2、14、15	OUT1	Output	Forward output.
3、5、10、13	GND	Ground	Device ground.
4	VCC	Power	Power supply.
6、7、8、9	OUT2	Output	Reverse output.
11	IN2	Input	Reverse logic control.
12	IN1	Input	Forward logic control.

ESD RATING

Items	Description	Value	Unit
V _{ESD}	Human body model for all pins	±2000	V

JEDEC specification JS-001

RECOMMENDED OPERATING CONDITIONS

Parameter	Symbol	Min	Max	Units
Power supply voltage range	VCC	6.8	40	V
Logic input voltage range	V _{IN_X}	-0.3	6	V
Output continuous current	I _{OUT_X}	0	7.0	A
Logic input frequency	F _{IN_X}	0	50	kHz

ELECTRICAL CHARACTERISTICS

($T_A = 25^\circ\text{C}$, over recommended operating conditions unless otherwise noted.)

Parameter	Symbol	Conditions	Min	Typ.	Max	Unit
Power supply (VCC)						
Operation voltage	V_{VCC}		6.8		40	V
Shutdown current	I_{SDT}	VCC=24V, IN1=IN2=0V, no load			1	μA
Standby current	I_{BRAKE}	VCC=24V, IN1=IN2=5V or IN1=5V & IN2=0V or IN1=0V & IN2=5V, no	0.3	0.6	1	mA
PWM current	I_{PWM}	VCC=24V, IN1=5V, IN2=50kHz, no load	1	1.5	3	mA
Turn-on time	t_{WAKE}	Sleep mode to active mode delay	10	15	20	μs
Auto-sleep Turn-off time	$t_{AUTOSLEEP}$	Active mode to autosleep mode delay	0.8	1	1.5	ms
Undervoltage lockout	UVLO	VCC rising	4.6	4.7	4.9	V
Logic inputs						
Input logic high	V_{INH}		1.5		6	V
Input logic low voltage	V_{INL}				1.2	V
Input logic high	I_{INH}	VCC = 24V, VIN = 5V		50	100	μA
Input logic low current	I_{INL}	VCC = 24V, VIN= 0V			1	μA
H-bridge FETs						
FETs on resistance	$R_{ds(on)}$	$I_{LOAD}=1\text{A}$, HS+LS		45		m Ω
FETs on resistance	$R_{ds(on)}$	$I_{LOAD}=3\text{A}$, HS+LS		50		m Ω
Over temperature protection						
Thermal shutdown temperature (Note4)	T_{SD}			170		$^\circ\text{C}$
Thermal shutdown hysteresis (Note4)	T_{HYS}			40		$^\circ\text{C}$
Over current protection						
Overcurrent	I_{OCP}	VCC = 24V		13.0		A
Overcurrent deglitch	t_{OCP}			2.5		μs

Note 1: Absolute Maximum Ratings are those values beyond which the life of a device may be impaired.

Note 2: Power dissipation and thermal limits must be observed.

Note 3: T_J is calculated from the ambient temperature T_A and power dissipation P_D according to the following formula: $T_J = T_A + P_D \times \theta_{JA}$. The maximum allowable continuous power dissipation at any ambient temperature is calculated by $P_{D(MAX)} = (T_{J(MAX)} - T_A) / \theta_{JA}$.

Note 4: Thermal shutdown threshold and hysteresis are guaranteed by design.

OPERATION

Bridge Control

The TMI8140 output consists of 4 internal P+N channel MOSFETs that are designed to drive high current. These outputs are controlled by the two logic inputs IN1 and IN2 as listed in Table 1.

Table 1. H-Bridge Control

IN1	IN2	OUT1	OUT2	DESCRIPTION
L	L	High-Z	High-Z	Coast; H-bridge disabled to High-Z
L	H	L	H	Reverse (Current OUT2 →OUT1)
H	L	H	L	Forward (Current OUT1 →OUT2)
H	H	L	L	Brake; low-side slow decay

Output Timing Diagram




Figure 2. TMI8140 Output Timing Diagram

Application Directions

The peripheral components on the typical application circuit as shown in Figure 1 are described as follows:

C1 and C2 are VCC input capacitors, the main functions are as follows:

1. Absorb the energy released by the motor to the power supply, stabilize the VCC power supply voltage, prevent the IC from being directly broken down due to the high surge voltage, and have the function of filtering ripple and interference noise.
2. At the moment when the motor starts, it can release current to help the motor start quickly.
3. The selection of the VCC input capacitor C2 needs to be based on the voltage stability of the VCC and the motor load current. If the VCC voltage wave is large or the motor load current is large, a larger capacitor value must be selected. It is recommended that the C2 capacitance is greater than 100uF.
4. C1 and C2 capacitors need to be as close to VCC as possible on the PCB configuration.

Work Mode Directions

Basic working mode:

1. Forward mode, defined as: $IN2=L$, $IN1=H$, then $OUT2=L$, $OUT1=H$;
2. Reverse mode, defined as: $IN2=H$, $IN1=L$, then $OUT2=H$, $OUT1=L$;
3. Brake mode, defined as: $IN2=H$, $IN1=H$, then $OUT2=L$, $OUT1=L$;
4. Coast mode, defined as: $IN2=L$, $IN1=L$, at this time $OUT2=Open$, $OUT1=Open$.




Figure 3. TMI8140 Work Modes

Thermal Shutdown (TSD) and Over Current Protection (OCP)

When the IC temperature exceeds 170°C (typical value), the overheating protection circuit of the built-in IC will forcibly turn off part of the driving MOS transistors to ensure the safety of customer products.

When the temperature of the IC drops to 130°C (typical), the IC will automatically resume to work quickly.

An analog current limit circuit on each MOSFET limits the peak current out of the device even in hard short circuit events. If the output current exceeds the overcurrent threshold $IOCP$ for longer than $tOCP$, all MOSFETs in the H-bridge will be disabled, until VDD power is removed, the MOSFETs will be re-enabled again.

Block Diagram





Figure 4. TMI8140 Block Diagram

PACKAGE INFORMATION

DFN6X5_15L




Symbol	Millimeter			Symbol	Millimeter		
	Min.	Nom.	Max.		Min.	Nom.	Max.
A	0.7	0.75	0.80	e2	0.69 BSC		
A1	0	0.02	0.05	e3	0.90 BSC		
b	0.20	0.25	0.30	e4	0.525 BSC		
b1	0.18 REF			e5	0.625 BSC		
b2	0.35	0.40	0.45	e6	1.45 BSC		
b3	0.25 REF			E	4.90	5.00	5.10
b4	0.30 REF			E2	3.40	3.50	3.60
b5	0.15	0.20	0.25	E3	4.50	4.60	4.70
b6	0.14 REF			E4	2.40	2.50	2.60
c	0.203 REF			L	0.45	0.50	0.55
D	5.90	6.00	6.10	L1	0.20 REF		
D2	1.20	1.30	1.40	L2	0.85	0.90	0.95
D3	1.75	1.85	1.95	L3	1.25	1.30	1.35
D4	1.15	1.25	1.35	K	0.40 REF		
e	0.50 BSC			K1	0.30 REF		
e1	0.76 BSC						

Notes:

1. Refer to JEDEC MS-012AA
2. All dimensions are in millimeter

TAPE AND REEL INFORMATION


TAPE DIMENSIONS: DFN6*5-15L



Unit: mm

E	F	P2	D	D1	P0	P0
1.7±0.10	5.50±0.05	2.00±0.05	1.50 ^{+0.10} ₀	1.50MIN2	4.00±0.10	40.0±0.10
W	P	A0	B0	K0	t	
12.0 ^{+0.20} _{-0.10}	8.00±0.10	5.30±0.10	6.30±0.10	1.20±0.10	0.30±0.05	

REEL DIMENSIONS: DFN6*5-15L



Unit: mm

A	B	C	D	E	F	T1
Ø 330±1	12.7±0.5	16.5±0.3	Ø 99.5±0.5	Ø 13.6±0.2	2.8±0.2	1.9±0.2

Note:

- 1) All Dimensions are in Millimeter
- 2) Quantity of Units per Reel is 5000
- 3) MSL level is level 3.

Important Notification

This document only provides product information. Xi'an TOLL Microelectronic Inc. (TMI) reserves the right to make corrections, modifications, enhancements, improvements, and other changes to its products and to discontinue any product without notice at any time.

Xi'an TOLL Microelectronic Inc. (TMI) cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a TMI product. No circuit patent licenses are implied.

All rights are reserved by Xi'an TOLL Microelectronic Inc.

[http:// www.toll-semi.com](http://www.toll-semi.com)