



SPECIFICATIONS

Rated Current:1.5AMP

Contact Resistance:20mΩ Max

Withstand Voltage:500V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:-40°C to +105°C


Contact Material:Brass

Contact Plating:Au or Sn Over Ni


Insulator Material:Polyester(UL94V-0)

Standard: PA6T

Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 5 seconds)



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



Ordering Information

1320 12 XX X N XX S XXX X 01

No.of
Pins
Per Row
1x40

Insulator Material

Option

A=BK-PBT
B=BK-PA66
C=BK-PA6T
D=BK-PA46
E=BK-PA9T
F=BK-LCP



Contact Plating

G0:0.8U" Gold
G1:1U" Gold
G2:1.5U" Gold
G3:2U" Gold
G4:3U" Gold
S0:Gold Flash/Tin
SN:Tin

Pin Length

Post

A=Tray
T=Tube
O=Pe
R=Tape&Reel
P=Tube&Reel



Dimension antitheses list

ITEM	PC	PA	L
Standard	2.80	3.90	8.70
Alternate			

OPERATION

DRAW

卢能

2016.9.10

SCALE

FIT

深圳市连盛精密连接器有限公司

X.X

±0.30

CHECK

X.XX

±0.20

APPROVE

X.XXX

±0.10

Angle

±3°

DIM

TOL

UNIT

mm

SIZE

A4

SHEET

1/1

PROJ.

◆

PART NO.

1010200034

TITLE:

2.0PH H=2.0 2xNpin DIP

1

2

3

4

5

6

7

8

9