

Features

- Vin Range Up to 40V
- Output Range: 2.6V~5.0V
- Maximum Output Current: 500mA
- PSRR: 75dB@1KHz
- Dropout Voltage: 200mV@I_{OUT}=100mA
- Ultra Low Quiescent Current: 2μA Typ.
- Output Voltage Tolerances of ±2% Over the Temperature Range
- Internal Thermal Overload Protection
- Built-in Foldback Current Limit

Applications

- E-meters, Water Meters and Gas Meters
- Cellphones, Radiophone, Digital Cameras
- Fire Alarm, Smoke Detector
- Appliances and White Goods


General Description

The HT7550-H is ultra-low quiescent current regulator features and low dropout voltage. With 2μA quiescent current at no load. The HT7550-H retains all of the features that are common to low dropout regulators including a low dropout PMOS pass device, foldback current limiter, and thermal shutdown.

The HT7550-H has 40V maximum operating voltage, excellent load transient response, and -40°C to 125°C operating temperature range, and ±2% output voltage tolerance over the entire output current, input voltage, and temperature range.

The HT7550-H regulators are available in standard SOT-89 packages.

Block Diagram



Pin Assignment

SOT-89 (Top View)




Table2: HT7550-H(SOT-89 PKG)

PIN NO.	PIN NAME	FUNCTION
1	GND	GND pin
2	VIN	Input voltage pin
3	VOUT	Output voltage pin



Absolute Maximum Ratings

Input Voltage.....-0.3V to 45V

Storage Temperature-55℃ to 150℃

 V_{EN}-0.3V to V_{IN}

Lead Temperature(Soldering, 10 sec.)260℃

 V_{OUT}-0.3V to 12V

Junction Temperature..... -40℃ to 125℃

ESD Rating.....5.5kV

Note: These are stress ratings only. Stresses exceeding the range specified under “Absolute Maximum Ratings” may cause substantial damage to the device. Functional operation of this device at other conditions beyond those listed in the specification is not implied and prolonged exposure to extreme conditions may affect device reliability.

Electrical Characteristics


The following specifications apply for $V_{IN}=12V$, $I_{OUT}=1mA$, $C_{IN}=C_{OUT}=10\mu F$, $T_J=25^\circ C$, unless specified otherwise.

SYMBOL	ITEMS	CONDITIONS	MIN	TYP	MAX	UNIT
V_{IN}	Input Voltage		2.7		40	V
V_{OUT}	Output Range		2.6		5.0	V
ΔV_{OUT}	Output Voltage Accuracy		-2	V_{OUT}	2	%
I_Q	Quiescent Current	$V_{IN} = V_{OUT} + 1V$	--	2	--	μA
V_{DROP}	Dropout Voltage	$I_{OUT}=100mA$	--	0.45	--	V
		$I_{OUT}=300mA$	--	0.75	--	
ΔV_{LINE}	Line Regulation	$V_{IN} = V_{OUT} + 1V$ to 40V, or $V_{IN} = 5V$ to 40V, if $V_{OUT} < 4V$	--	30	--	mV
ΔV_{LOAD}	Load Regulation	$I_{OUT} = 1mA$ to 100mA	--	20	--	mV
		$I_{OUT} = 1mA$ to 250mA	--	30	--	
PSRR	Power Supply Rejection Rate $V_{IN}=V_{OUT}+1V$ Ripple=0.2Vp-p $I_{OUT}=10mA$	Freq.=1kHz	--	75	--	dB
		Freq.=100kHz	--	45	--	
I_{SHORT}	I_{OUT} @ V_{OUT} Short to Ground	$V_{IN}=6V$, $V_{OUT}=0V$	--	50	--	mA
T_{SD}	Thermal Shutdown		--	150	--	℃
T_{HY}	Thermal Shutdown Hysteresis		--	130	--	℃

Note1: The parameters of C_{in} and C_{out} must be greater than 4.7 μF .


Application Circuits

Typical Application Circuits



Note1: The parameters of Cin and Cout must be greater than 4.7uF.

External Power Dissipation




Note2: The resistance value of R1 should be set to 0.25Ω.


Typical Performance Characteristics

$C_{IN}=10\mu F$, $C_{OUT}=10\mu F$, $T_J=25^{\circ}C$, unless specified otherwise


(1) Quiescent Current vs Input Voltage




(2) Ground Pin Current vs Output Current




(3) Output Voltage vs Input Voltage




(4) Output Voltage vs Output Current




(5) Dropout Voltage vs Output Current




(6) Output Voltage vs Output Current




(7) Quiescent Current vs Temperature




(8) Output Voltage vs Temperature




(9) Dropout Voltage vs Temperature




(10) PSRR VS Frequency




(11) Input Transient Response




(12) Load Transient Response




(13) Power ON



(14) Power OFF



SOT-89 Outline Dimensions



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	1.400	1.600	0.055	0.063
b	0.320	0.520	0.013	0.020
b1	0.400	0.580	0.016	0.023
c	0.350	0.440	0.014	0.017
D	4.400	4.600	0.173	0.181
D1	1.550 REF.		0.061 REF.	
E	2.300	2.600	0.091	0.102
E1	3.940	4.250	0.155	0.167
e	1.500 TYP.		0.060 TYP.	
e1	3.000 TYP.		0.118 TYP.	
L	0.900	1.200	0.035	0.047