

MBRD1045CT THRU MBRD10200CT

SURFACE MOUNT SCHOTTKY BARRIER RECTIFIER

TO-252 Surface Mount Schottky Barrier Rectifier

Features

- For surface mounted applications
- High forward surge current capability
- High reliability
- High current capability

Applications

For use in low voltage high frequency inverters, free wheeling,DC/DC converters, and polarity protection applications.

Mechanical Data




- Case: TO-252
Molding compound meets UL 94V-0 flammability rating, RoHS-compliant, halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750,Method 2026

Function Diagram

Reverse Voltage
45-200 V

Forward Current
10 Ampere

TO-252







Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	MBRD 1045CT	MBRD 1060CT	MBRD 10100CT	MBRD 10150CT	MBRD 10200CT
Device marking code			MBRD 1045CT	MBRD 1060CT	MBRD 10100CT	MBRD 10150CT	MBRD 10200CT
Maximum Repetitive Peak Reverse Voltage	V_{RRM}	V	45	60	100	150	200
Maximum RMS Voltage	V_{RMS}	V	32	42	70	105	140
Maximum DC blocking Voltage	V_{DC}	V	45	60	100	150	200
Maximum Average Forward Rectified Current @60Hz sinewave, Resistance load,TL (Fig.1)	$I_{F(AV)}$	A	10				
Non-repetitive Peak Forward Surge Current @ t=8.3ms Half-sine wave	I_{FSM}	A	150				
Storage temperature	T_{stg}	°C	-55 ~ +150				
Junction temperature	T_j	°C	-55 ~ +150				
Typical Thermal Resistance	$R_{\theta JC}$	°C /W	5				
	$R_{\theta JA}$	°C /W	100				

● Electrical Characteristics (Ta=25°C Unless otherwise noted)

PARAMETER	TEST CONDITIONS	SYMBOL	UNIT	MBRD 1045CT	MBRD 1060CT	MBRD 10100CT	MBRD 10150CT	MBRD 10200CT
Maximum instantaneous forward voltage	I _F =5A	V _F	V	0.60	0.75	0.85	0.90	
Maximum DC reverse currentat rated DC blocking voltage	V _R =V _{DC} , T _A =25°C	I _{R1}	mA	0.1		0.02		
	V _R =V _{DC} , T _A =125°C	I _{R2}		5.0		2.0		

● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)



● Ordering Information

PACKAGE	PACKAGE CODE	UNIT WEIGHT(g)	REEL(pcs)	BOX(pcs)	CARTON(pcs)	DELIVERY MODE
TO-252	R3	0.305	2500	5000	45000	13"

● Package Outline Dimensions (TO-252)

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	6.50	6.70	0.256	0.264
B	5.10	5.46	0.201	0.215
C	1.40	1.80	0.055	0.071
D	6.00	6.20	0.236	0.244
E	10.00	10.40	0.394	0.409
F	2.16	2.36	0.085	0.093
G	0.66	0.86	0.026	0.034
Φ	1.05	1.35	0.041	0.053
H	0.46	0.58	0.018	0.023
J	2.20	2.40	0.087	0.094
K	-	0.30	-	0.012
L	0.89	2.29	0.035	0.090
M	2.73	3.08	0.107	0.121
N	0.43	0.58	0.017	0.023

● Suggested Pad Layout

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
a	3.70	-	0.146	-
b	4.37	-	0.172	-
X	-	5.80	-	0.228
X1	-	1.20	-	0.047
Y	-	5.85	-	0.230
Y1	-	2.00	-	0.079