






1	2	3	4	5	6	7
REV.	ZONE	DESCRIPTION			DESIGN	DATE
B		NEW				



X.	± 0.50	X°	± 2°
X	± 0.30	X°	± 1°
.XX	± 0.10	.XX°	± 0.5°
.XXX	± 0.05		



A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CCI	B8	SBU2
A6	DPI	B7	DP2
A7	DNI	B6	DP1
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

SPECIFICATIONS:


1. ELECTRICAL CHARACTERISTICS:

- 1-1. CONTACT RESISTANCE: 30m Ω MAX.
1-2. DIELECTRIC WITHSTANDING VOLTAGE: 100V AC FOR ONE MINUTE.
1-3. INSULATION RESISTANCE: 100M Ω MIN. MEASURED BY 500 VDC

2. MECHANICAL CHARACTERISTICS:

- 2-1. INSERTION FORCE :0.5-2.0Kgf(REF.)
2-2. WITHDRAWAL FORCE :0.8-2.0Kgf(REF.)

3. LIFE TEST: 10,000 CYCLES.



H= MM						
9.30	10.00	10.50	12.40	13.10	13.70	15.00

6	SHELL	STAINLESS STEEL	NI Plated	1PCS
5	SHIELDING PLATE	STAINLESS STEEL	---	1PCS
4	MD	HIGH TEMPERATURE PLASTIC	BLACK	1PCS
3	CONTACT	COPPER ALLOY	Au/NI Plated	1SET
2	CONTACT	COPPER ALLOY	Au/NI Plated	1SET
1	HOUSING	HIGH TEMPERATURE PLASTIC	BLACK	1PCS
NO.	DESCRIPTION	MATERIAL	REMARKS	QTY

UNITS MM	深圳市富港科技有限公司		
MAT'L	TITLE: TYPE-C 16PIN 180度立式贴片SMT母座		
FINISH	APPD: C	Y	DWG NO.: ST-C-JTF5-16PC-L15.0
Q'TY	CHKD: L	P J	SCALE SHEET REV.
DR:	□	F	1/1 1/1 A1