





SK-23D29-GXXX


SS: Straight shank
SK: 横柄

G-Switch P/N

Switch Height (mm)
G080=8.0mm



RECOMMENDED PCB LAYOUT
TOLERANCE: ±0.05



CIRCUIT DIAGRAM

- G-Switch Specification:**
- 1. Operating temperature range: -40°C ~ +85°C
 - 2. Rating: 50mA.12V DC
 - 3. Insulation resistance: 100MΩ min.100V DC
 - 4. Dielectric strength: 250V AC for 1 min
 - 5. Contact resistance: 100mΩ max.
 - 6. Terminals arrangement: 2P3T
 - 7. Travel: 2.0±0.1mm

7	STEEL BALL	STEEL	NATURAL
6	SPRING	STEEL WIRE	NATURAL
5	CONTACT CLIP	PBS STRIP	Ag PLATED
4	TERMINAL	BRASS STRIP	Ag PLATED
3	BASE	PHENOLIC RESIN	NATURAL
2	KNOB	POM	BLACK
1	FRAME	STEEL STRIP	NI PLATED
NO.	PART NAME	MATERIAL	REMARK

Process Capable

RoHS
Compliant
EU RoHS Standards

Compliant
Halogen Free

SCALE: 1:1	UNIT: mm	Title: Horizontal Slide Switch DIP 14×6.5×H8.5mm			
SIZE: A4		Molde Code: SK-23D29-GXXX			
Unless otherwise General Tolerance: within 1.5mm over 1.5 ±0.10 ±0.20		DRAWN	CHECKED	APPROVED	DATE
		Xia	Chen	Chen	2023.02.01

品赞科技®
www.dg-switch.com

REV: A0	SHEET: 1/1
---------	------------