




材料及电镀

1. 塑件主体: PA66 ,
2. 焊 针: 黄铜, 镀镍


电气性能

额定电压: 300V
额定电流: 8A
接触电阻: 20mΩ (Max)
绝缘电阻: 500MΩ\DC1000V
耐 电 压: AC1500V\1Min

机械性能

温度范围: -40℃ ~ +105℃
瞬时温度: +250℃ , 5秒

2	插针	铜	镀镍	
1	基座	PA66	绿色	
序 号	品 名	材 质	电镀/颜色	备 注

	深圳市虹成电子有限公司		品 名 TITLE	接线端子																									
			料 号 PART NO	HC-JXDZRC-3. 81-10P																									
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1 : 1																										
<table border="1"><thead><tr><th colspan="4">公差参数</th></tr><tr><th>Poles</th><th>Dim</th><th>DimP</th><th>DimL</th></tr></thead><tbody><tr><td>2-6P</td><td>±0.10</td><td>±0.20</td><td></td></tr><tr><td>7-12P</td><td>±0.20</td><td>±0.30</td><td></td></tr><tr><td>13-18P</td><td>±0.25</td><td>±0.40</td><td></td></tr><tr><td>19-24P</td><td>±0.30</td><td>±0.50</td><td></td></tr></tbody></table>		公差参数				Poles	Dim	DimP	DimL	2-6P	±0.10	±0.20		7-12P	±0.20	±0.30		13-18P	±0.25	±0.40		19-24P	±0.30	±0.50		单 位 UNIT	MM	制 图 DRAW	AhYe
公差参数																													
Poles	Dim	DimP	DimL																										
2-6P	±0.10	±0.20																											
7-12P	±0.20	±0.30																											
13-18P	±0.25	±0.40																											
19-24P	±0.30	±0.50																											
<table><tr><td>X. xxx</td><td>±0.15</td></tr><tr><td>X. xx</td><td>±0.25</td></tr><tr><td>X. x</td><td>±0.35</td></tr></table>		X. xxx	±0.15	X. xx	±0.25	X. x	±0.35	张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云																		
X. xxx	±0.15																												
X. xx	±0.25																												
X. x	±0.35																												
<table><tr><td colspan="2">ANGULAR:</td></tr><tr><td>X. xx°</td><td>±1°</td></tr><tr><td>X. x°</td><td>±3°</td></tr><tr><td>X. °</td><td>±5°</td></tr></table>		ANGULAR:		X. xx°	±1°	X. x°	±3°	X. °	±5°	版 本 REV	A	批 准 APPROVE	赵亮亮																
ANGULAR:																													
X. xx°	±1°																												
X. x°	±3°																												
X. °	±5°																												
																													

