


MOSFET

11A,650V,380mΩ,N-CHANNEL MOSFET

Features

- ◆ Low gate charge
- ◆ Low Ciss
- ◆ Fast switching
- ◆ 100% avalanche tested
- ◆ Improved dv/dt capability
- ◆ RoHS 2.0 Compliant

Parameter	Values	Unit
BV_{dss}	650	V
I_D	11	A
$R_{Dson}(max)$	380	mΩ
$V_{GS(th)}(Typ)$	3	V



Ordering Code	Marking	Package	Packaging
X380N65JHV8	X380N65JHV8	PDFN5*6-8L	Tape and Reel

Absolute Maximum Ratings($T_C=25^{\circ}C$, unless otherwise noted)

Parameter	Symbol	Values			Unit	Note/Test Conditions
		Min	Typ	Max		
Drain-Source Voltage	V_{DSS}	-	-	650	V	-
Gate-Source Voltage	V_{GS}	-20	-	20	V	-
Continuous Drain Current	I_D	-	-	11	A	$T_C=25^{\circ}C$
		-	-	6.6	A	$T_C=100^{\circ}C$
Pulsed Drain Current(Note 1)	I_{DM}	-	-	44	A	
Single Pulse Avalanche Energy	E_{AS}	-	-	61	mJ	$L=10mH, V_D=50V$
Maximum Power Dissipation	P_D	-	-	55	W	$T_C=25^{\circ}C$
Reverse Diode dV/dt (Note 2)	dv/dt	-	-	15	V/ns	
Operating Junction and Storage Temperature Range	T_J, T_{STG}	-55	-	150	$^{\circ}C$	-
Soldering temperature, wave soldering only allowed at leads(1.6mm from case for 10s)	T_L	-	-	260	$^{\circ}C$	

Thermal Characteristics

Parameter	Symbol	Values			Unit	Note/Test Conditions
		Min	Typ	Max		
Thermal resistance , channel to Case	$R_{th(ch-c)}$	-	2.2	-	$^{\circ}C/W$	-

Electrical Characteristics ($T_j=25^{\circ}\text{C}$, unless otherwise noted)

Static characteristics

Parameter	Symbol	Values			Unit	Note/Test Conditions
		Min	Typ	Max		
Drain-Source Breakdown Voltage	BV_{DSS}	650	-	-	V	$V_{GS}=0V, I_D=250\mu A$
Zero Gate Voltage Drain Current	I_{DSS}	-	-	1	μA	$V_{DS}=650V, V_{GS}=0V$
Gate-Body Leakage Current, Forward	I_{GSSF}	-	-	100	nA	$V_{GS}=20V, V_{DS}=0V$
Gate-Body Leakage Current, Reverse	I_{GSSR}	-	-	-100	nA	$V_{GS}=-20V, V_{DS}=0V$
Gate-Source Threshold Voltage	$V_{GS(th)}$	2	-	4	V	$V_{DS}=V_{GS}, I_D=250\mu A$
Drain-Source On-State Resistance	$R_{DS(on)}$	-	310	380	m Ω	$V_{GS}=10V, I_D=5.5A$
Gate Resistance	R_g	-	9.9	-	Ω	$V_{GS}=0V, V_{DS}$ Open, $f=1\text{MHz}$
Forward Transconductance	g_{fs}	-	3.7	-	S	$V_{DS}=5V, I_D=5.5A$

Dynamic characteristics

Parameter	Symbol	Values			Unit	Note/Test Conditions
		Min	Typ	Max		
Input Capacitance	C_{iss}	-	750	-	pF	$V_{DS}=400V, V_{GS}=0V, f=500\text{KHz}$
Output Capacitance	C_{oss}	-	25	-	pF	
Reverse Transfer Capacitance	C_{rss}	-	5	-	pF	
Turn-On Delay Time	$t_{d(on)}$	-	14.6	-	ns	$V_{DD}=375V, R_G=10\Omega, V_{GS}=10V, I_D=66A$
Turn-On Rise Time	t_r	-	2	-	ns	
Turn-Off Delay Time	$t_{d(off)}$	-	117.2	-	ns	
Turn-Off Fall Time	t_f	-	21.2	-	ns	

Gate charge characteristics

Parameter	Symbol	Values			Unit	Note/Test Conditions
		Min	Typ	Max		
Total Gate Charge	Q_g	-	21	-	nC	$V_{DS}=520V, I_D=11A, V_{GS}=10V$
Gate-Source Charge	Q_{gs}	-	6.1	-	nC	
Gate-Drain Charge	Q_{gd}	-	9.5	-	nC	


Reverse diode

Parameter	Symbol	Values			Unit	Note/Test Conditions
		Min	Typ	Max		
Continuous Diode Forward Current	I_S	-	-	11	A	-
Pulsed Diode Forward Current	I_{SM}	-	-	44	A	-
Diode Forward Voltage	V_{SD}	-	-	1.5	V	$I_S=5.5A, V_{GS}=0V$
Reverse Recovery Time	t_{rr}	-	314	-	ns	$V_R=35V, I_F=10A, di/dt=100A/\mu s$ (Note2)
Reverse Recovery Charge	Q_{rr}	-	3.65	-	nC	


Notes

1. Repetitive Rating;pulse width limited by maximum junction temperature.
2. Pulse width $\leq$ 300us,duty cycle $\leq$ 2%.


RATING AND CHARACTERISTIC CURVES




Peak Diode Recovery dv/dt Test Circuit




Peak Diode Recovery dv/dt Waveforms




Switching Test Circuit




Switching Waveforms




Gate Charge Test Circuit



Gate Charge Waveform



Unclamped Inductive Switching Test Circuit



Unclamped Inductive Switching Waveforms

RATING AND CHARACTERISTIC CURVES

Figure.1 Output Characteristics




Figure.2 Transfer Characteristics




Figure.3 $R_{ds(on)}$ vs Drain Current and Gate Voltage




Figure.4 $R_{ds(on)}$ vs Gate Voltage




Figure.5 Rds(on) vs. Temperature




Figure.6 Vgs(th) vs. Temperature




Figure.7 BVdss vs. Temperature




Figure.8 Capacitance Characteristics




Figure.9 Gate Charge Characteristics




Figure.10 Body-diode Forward Characteristics




Figure.11 Power Dissipation




Figure.12 Drain Current Derating







Figure.13 Maximum Effective Thermal Impedance , Junction to Case



Package Outline: PDFN5*6-8L



RECOMMENDED LAND PATTERN



	MIN	NOM	MAX
A	0.90	1.00	1.10
b	0.25	0.35	0.50
c	0.10	0.20	0.30
D	4.80	5.00	5.30
D1	4.90	5.10	5.50
D2	3.92	4.02	4.20
E	5.65	5.75	5.85
E1	5.90	6.05	6.20
E2	3.325	3.525	3.775
E3	0.80	0.90	1.00
e		1.27	
L	0.40	0.55	0.70
L1		0.65	
L2	0.00		0.15
K	1.00	1.30	1.50