





7~9 Pin




10~16 Pin



SPECIFICATIONS

1. Current Rating: 3A AC, DC
2. Voltage Rating: 250V AC, DC
3. Temperature Range: -40℃~ +105℃
4. Contact Resistance: 20mΩ Max
5. Insulation Resistance: 1000mΩ Min
6. Withstanding Voltage: 800V AC/minute
7. Material: Wafer PA6T UL94-V0
PIN Brass Tin-plated
Solder tab Brass Tin-Plated

Circuit	Part NO.	Dimensions mm			
		A	B	C	D
2	HC-PAE-2AWT	2.00	8.00	4.60	6.20
3	HC-PAE-3AWT	4.00	10.00	6.60	8.20
4	HC-PAE-4AWT	6.00	12.00	8.60	10.20
5	HC-PAE-5AWT	8.00	14.00	10.60	12.20
6	HC-PAE-6AWT	10.00	16.00	12.60	14.20
7	HC-PAE-7AWT	12.00	18.00	14.60	16.20
8	HC-PAE-8AWT	14.00	20.00	16.60	18.20
9	HC-PAE-9AWT	16.00	22.00	18.60	20.20
10	HC-PAE-10AWT	18.00	24.00	20.60	22.20
11	HC-PAE-11AWT	20.00	26.00	22.60	24.20
12	HC-PAE-12AWT	22.00	28.00	24.60	26.20
13	HC-PAE-13AWT	24.00	30.00	26.60	28.20
14	HC-PAE-14AWT	26.00	32.00	28.60	30.20
15	HC-PAE-15AWT	28.00	34.00	30.60	32.20
16	HC-PAE-16AWT	30.00	36.00	32.60	34.20

			GENERAL TOLERANCE	制图 DRAWING	02	 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审核 CHECK					
			X.X ±0.30	批准 APPROVAL		产品名称 TITLE	PAE (2.00) 单排卧贴	版本 REV.	A
1	初版发行		X.XX ±0.20	比例 SCALE		产品料号 PART NO.	HC-PAE-NAWT	单位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	X.XXX ±0.10	投影 Projection		材料 MATERIAL		页次 SHEET	1/1
			Angle ±3.0°						