











RECOMMENDED PCB LAYOUT (component side)(TOP VIEW)
DEFAULT TOLERANCES:±0.05/PCB THICKNESS:1.0MM
■ NO PATIERN AREA

NOTES

MATERIAL

- 1.HOUSING MATERIAL: LCP BLACK UL94V-0.
- 2.CONTACT MATERIAL: PHOSPHOR BRONZE T=0.25mm.
- 3.PLATING: GOLD PLATING ON CONTACT AREA,100u" MATTE-TIN ON SOLDER TAIL50u"NICKEL UNDERPLATED OVERALL.
- 4.SHIELD: SUS T=0.20mm WITH NICKEL PLATED.

ELECTRICAL


- 1.VOLTAGE RATING: 125 VAC RMS.
- 2.CURRENT RATING: 1.5 AMP.
- 3.CONTACT RESISTANCE: 40 MILLIOHMS MAX.
- 4.INSULATION RESISTANCE: 500 MEGOHMS MIN @ 100V DC .
- 5.DIELECTRIC DIELECTRIC RESISTANCE: 500V DC RMS 50Hz. 1MIN.

MECHANICAL

- 1.DURRABILITY: 750 CYCLES MIN.
2. MATING/UNMATING FORC: 2.24 KG.F MAX.

ENVIRONMENTAL:

- 1.OPERATION: -40℃~+85℃.
- 2.STORAGE: -40℃~+85℃.

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.:±0.35	X':±3"	PART NO. RJ45-5020-8P	TITLE: RJ45 9.9H 流板5.65 半包 A款无灯		
X.X:±0.25	X.X':±2"				
X.XX:±0.15	X.XX':±1"				
UNITS	mm	DESIGN:	Ethan		
MATERILA	— — —	CHED:	Olvia		
FINISH	— — —	APPD:	Ava		
				SCALE	SHEET
				N:A	1/1