





Rev No.	Description of Revision	Date	Name	Approved	ECN No.




MID. B

RECOMMENDED P.C.B LAYOUT TOP VIEW  
(GENERAL TOLERANCE ±0.10)

## Specifications:

1. Rated Voltage : 125V AC/DC
2. Rated Current : 2A AC,DC
3. Withstand Voltage : 200V AC/minute
4. Contact Resistance: 50mΩ (MAX.)
5. Insulation Resistance: 100mΩ (MIN.)
6. Storage Temperature Range: -40°C~+85°C;
7. Operation Temperature Range: -25°C~+70°C;

PIN数	MID. A	MID. B	MID. C
2P	2.00	8.00	2.00
3P	4.00	10.00	4.00
4P	6.00	12.00	6.00
5P	8.00	14.00	8.00
6P	10.00	16.00	10.00



③	端子	黄铜H65	镀亮锡	6PCS
②	固定片	黄铜H65	镀亮锡	2PCS
①	塑胶主体	LCP	本色	1PCS
序号	配件名称	材质	电镀/颜色	数量

UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: HX-PH2.0-6ALB		
DECIMALS:	ANGLES	Ordwn:	PART NO. WF004-LT20006-01	
X. ±0.15	X. ±2°	Checked:	黄彬	
X.X ±0.10	X.X* ±1°	Approved:	张伟	
X.XX ±0.05	X.XX* ±0.5°	Approved:	罗小春	
X.XXX ±0.03		REV.	A	
CUSTOMER COPY				

®  
韩下 HANXIA 深圳市韩下电子有限公司



® 深圳市韩下电子有限公司  
Shenzhen Hanxia Electronic Co., Ltd  
Tel: 0755-23086569

## 承 认 书

## SPECIFICATION FOR APPROVAL

产品编码

Material code:

---

产品名称 Project:

针座

---

规格型号 Part No:

HX-PH2.0-6ALB

---

贵公司承认印 Approval signatures

料号/Part No.	签章/Signatures

日期 Date:

拟制/Drawn	黄彬	
审核/Check	张伟	
批准/Approved	罗小春	