



# N-channel Enhancement Mode Power MOSFET

#### 芯天下技术股份有限公司

XTX Technology Inc.

Tel: (+86 755) 28229862 Fax: (+86 755) 28229847

Web Site: http://www.xtxtech.com/ Technical Contact: fae@xtxtech.com

\* Information furnished is believed to be accurate and reliable. However, XTX Technology Inc. assumes no responsibility for the consequences of use of such information or for any infringement of patents of other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent rights of XTX Technology Inc. Specifications mentioned in this publication are subjected to change without notice. This publication supersedes and replaces all information previously supplied. XTX Technology Inc. products are not authorized for use as critical components in life support devices or systems without express written approval of XTX Technology Inc. The XTX logo is a registered trademark of XTX Technology Inc. All other names are the property of their respective own.



### **FEATURES**

◆ 30V, 100A

 $R_{DS(ON)}\!<3.6m\Omega\ @\ VGS=10V$ 


 $R_{DS(ON)} \leq 6.1 m\Omega @ VGS = 4.5V$ 


- ◆ Advanced Trench Technology
- ◆ Excellent R<sub>DS(ON)</sub> and Low Gate Charge
- ◆ Lead Free




- ◆ Load Switch
- ◆ PWM Application
- ◆ Power Management










Marking and Pin Assignment



**Schematic Diagram** 

#### PACKAGE MARKING AND ORDERING INFORMATION

OPN	Marking	Package	Quantity
BRT30N100P3	T30N100	TO-252-2L	2500pcs/Reel

### **ABSOLUTE MAXIMUM RATINGS**

Symbol	Definition		Ratings	Unit
$ m V_{DS}$	Drain-to-So	30	V	
$V_{GS}$	Gate-to-Sou	±20	V	
$I_{\mathrm{D}}$	Continuous Drain Current	$T_{\rm C} = 25^{\circ}{\rm C}$	100	A
ID		$T_C = 100$ °C	63	A
$I_{DM}$	Pulsed Drai	n Current (1)	400	A
Eas	Single Pulsed Av	alanche Energy (2)	156	mJ
$P_D$	Power Dissipat	tion, $T_C = 25^{\circ}C$	80	W
$R_{ heta JA}$	Thermal Resistance, J	Junction to Ambient <sup>(3)</sup>	32	°C/W
$R_{ heta JC}$	Thermal Resistanc	e, Junction to Case	1.6	°C/W
T <sub>J</sub> , T <sub>STG</sub>	Junction & Storage	Temperature Range	-55 ~ +150	°C



### **ELECTRICAL CHARACTERISTICS** (All test condition is T<sub>J</sub>=25°C, unless otherwise noted)

Symbol	Parameter	Condition	Min	Тур	Max	Unit	
Off Characte	eristics						
V <sub>(BR)DSS</sub>	Drain-Source Breakdown Voltage	$I_D=250\mu A,V_{GS}=0V$	30	-	-	V	
$I_{DSS}$	Zero Gate Voltage Drain Current	$V_{DS}=30V,V_{GS}=0V$	-	-	1	uA	
$I_{GSS}$	Gate-Body Leakage Current	$V_{DS} = 0V, V_{GS} = \pm 20V$	-	-	±100	nA	
On Characte	eristics						
V <sub>GS(TH)</sub>	Gate Threshold Voltage	$V_{DS} = V_{GS}, I_D = 250uA$	1.1	1.6	2.5	V	
D	Static Drain-Source ON-Resistance <sup>(4)</sup>	$V_{GS} = 10V, I_D = 30A$		2.6	3.6	mΩ	
R <sub>DS(ON)</sub>	Static Drain-Source On-Resistance	$V_{GS} = 4.5V, I_D = 20A$		3.7	6.1	mΩ	
Dynamic Ch	aracteristics						
$C_{iss}$	Input Capacitance		-	2789	-	pF	
$C_{oss}$	Output Capacitance	$V_{GS} = 0V, V_{DS} = 15V,$ f = 1MHz	-	365	-	pF	
$C_{rss}$	Reverse Transfer Capacitance		-	309	-	pF	
$R_{G}$	Gate resistance	V <sub>GS</sub> =0V, V <sub>DS</sub> =0V,f=1.0MHz	-	2.34	-	Ω	
Qg	Total Gate Charge		-	58	-	nC	
$Q_{gs}$	Gate Source Charge	$V_{GS} = 0$ to $10V$ $V_{DS} = 15V$ , $I_D = 30A$	-	12	-	nC	
Q <sub>gd</sub> Gate Drain("Miller") Charge			-	13	-	nC	
Switching Cl	haracteristics						
$t_{d(on)}$	Turn-On Delay Time		-	11	-	ns	
t <sub>r</sub>	Turn-On Rise Time	$V_{GS} = 10V, V_{DD} = 15V$	-	29	-	ns	
$t_{\rm d(off)}$	Turn-Off Delay Time	$I_D = 30A$ , $R_G = 3\Omega$	-	47	-	ns	
t <sub>f</sub> Turn-Off Fall Time			-	18	-	ns	
Drain-Source Diode Characteristics							
$I_S$	Continuous Source Current		-	-	100	A	
$ m V_{SD}$	Forward on voltage	$V_{GS} = 0V, I_S = 30A$	-	-	1.2	V	
Trr	Reverse Recovery Time	I - 20A 4:/4-100A/	-	16	-	ns	
Q <sub>rr</sub> Reverse Recovery Charge		$I_F = 30A$ , $di/dt = 100A/us$	-	7	-	nC	

#### Notes:

- 1. Repetitive Rating: Pulse Width Limited by Maximum Junction Temperature.
- 2.  $E_{AS}$  condition: Starting  $T_J$ =25°C,  $V_{DD}$ =15V,  $V_G$ =10V,  $R_G$ =25 $\Omega$ , L=0.5mH,  $I_{AS}$ =25A
- 3.  $R_{\theta JA}$  is measured with the device mounted on a 1 inch² pad of 2oz copper FR4 PCB
- 4. Pulse Test: Pulse Width  $\leq 300 \mu s,$  Duty Cycle  $\leq 0.5 \%.$



### TYPICAL PERFORMANCE CHARACTERISTICS

Figure 1: Output Characteristics




Figure 2: Typical Transfer Characteristics




Figure 3: On-resistance vs. Drain Current




Figure 4: Body Diode Characteristics




Figure 5: Gate Charge Characteristics





Figure 6: Capacitance Characteristics





#### TYPICAL PERFORMANCE CHARACTERISTICS

Figure 7: Normalized Breakdown voltage vs.
Junction Temperature




Figure 8: Normalized on Resistance vs. Junction Temperature




Figure 9: Maximum Safe Operating Area




Figure 10: Maximum Continuous Drain Current vs. Case Temperature




Figure 11: Normalized Maximum Transient Thermal Impedance





Figure 12: Peak Current Capacity





### **TEST CIRCUIT**




Figure 13: Gate Charge Test Circuit & Waveform




Figure 14: Resistive Switching Test Circuit & Waveform




Figure 15: Unclamped Inductive Switching Test Circuit& Waveform





Figure 16: Diode Recovery Test Circuit & Waveform



### **MARKING INFORMATION**





1st Line: XTX Logo

2nd Line: Part Number (T30N100)

3rd Line: Date Code (XXXX)


XX: Year

XX: Week (01 to 53)

Year	2021	2022	2023	2024	2025	2026	2027	2028	2029	2030	2031	2032	2033
Code	21	22	23	24	25	26	27	28	29	30	31	32	33



## **DETAIL PACKAGE OUTLINE DRAWING (TO-252-2L)**



GVATDOL	MILLIMETERS						
SYMBOL	MIN	NOM	MAX				
A	2.20	2.30	2.40				
A1	0.00	-	0.10				
b	0.66	-	0.86				
b1	0.65	0.76	0.81				
с	0.47	-	0.60				
c1	0.46	0.51	0.56				
D	6.50	6.60	6.70				
D1	5.10	5.46					
D2	4.83 REF.						
Е	6.00	6.10	6.20				
e	2.186	2.286	2.386				
L	9.80	10.10	10.40				
L1							
L2	1.40	1.50	1.60				
L3	1.80 REF.						
L4	0.60	0.80	1.00				
L5	0.90	-	1.25				
L6	0.15	-	0.75				
Φ	1.10	-	1.30				
θ	0		8°				
V		5.40 REF.					



## **REVISION HISTORY**

Number	Description
Rev 1.0	BRT30N100P3 datasheet release