







修 订	标 记	修 改 描 要	签 名	日 期
REV	NO	DESCRIPTION	SIGNATURE	DATE
		NEW DWG		2016-03-12

NOTES:


- 1.HUOSING: LCP HIGH-TEMP THERMOPLASTIC UL94V-0 COLOR:NATURE
- 2.ACTUATOR: LCP HIGH-TEMP THERMOPLASTIC UL94V-0 COLOR:BLACK
- 3.TERMINAL:PHOSPHOR BRONZE
PLATING:1*''GOLD FLASH OR 100~150*''TIN(LEAD FREE)
OVERALL 50~100*''NICKEL UNDER PLATED.
- 4.FITTING NAIL:PHOSPHOR BRONZE
PLATING:100~150*''TIN(LEAD FREE)
OVERALL 50~100*''NICKEL UNDER PLATED.
- 5.SPECIFICATION:
CURRENT RATING: 0.5A 50V AC/DC
CONTACT RESISTANCE: 30mΩ MAX
INSULATION RESISTANCE: 100MΩ AT 500V DC
OPERATING TEMPERATURE RANGE: -40°C~85°C
WITHSTANDING VOLTANG: 500V AC/minute



CABLE INSERT DIM.
SCALE 2:1



RECOMMENDED PCB PATTERN DIM.
TOLERANCE : ±0.05



NO.of contacts	Dimensions				NO.of contacts	Dimensions			
	A.	B.	C.	D.		A.	B.	C.	D.
40	27.00	19.50	24.10	27.50	69	41.50	34.00	38.60	42.00
41	27.50	20.00	24.60	28.00	70	42.00	34.50	39.10	42.50
42	28.00	20.50	25.10	28.50	71	42.50	35.00	39.60	43.00
43	28.50	21.00	25.60	29.00	72	43.00	35.50	40.10	43.50
44	29.00	21.50	26.10	29.50	73	43.50	36.00	40.60	44.00
45	29.50	22.00	26.60	30.00	74	44.00	36.50	41.10	44.50
46	30.00	22.50	27.10	30.50	75	44.50	37.00	41.60	45.00
47	30.50	23.00	27.60	31.00	76	45.00	37.50	42.10	45.50
48	31.00	23.50	28.10	31.50	77	45.50	38.00	42.60	46.00
49	31.50	24.00	28.60	32.00	78	46.00	38.50	43.10	46.50
50	32.00	24.50	29.10	32.50	79	46.50	39.00	43.60	47.00
51	32.50	25.00	29.60	33.00	80	47.00	39.50	44.10	47.50
52	33.00	25.50	30.10	33.50	81	47.50	40.00	44.60	48.00
53	33.50	26.00	30.60	34.00	82	48.00	40.50	45.10	48.50
54	34.00	26.50	31.10	34.50	83	48.50	41.00	45.60	49.00
55	34.50	27.00	31.60	35.00	84	49.00	41.50	46.10	49.50
56	35.00	27.50	32.10	35.50	85	49.50	42.00	46.60	50.00
57	35.50	28.00	32.60	36.00	86	50.00	42.50	47.10	50.50
58	36.00	28.50	33.10	36.50	87	50.50	43.00	47.60	51.00
59	36.50	29.00	33.60	37.00	88	51.00	43.50	48.10	51.50
60	37.00	29.50	34.10	37.50	89	51.50	44.00	48.60	52.00
61	37.50	30.00	34.60	38.00	90	52.00	44.50	49.10	52.50
62	38.00	30.50	35.10	38.50	91	52.50	45.00	49.60	53.00
63	38.50	31.00	35.60	39.00	92	53.00	45.50	50.10	53.50
64	39.00	31.50	36.10	39.50	93	53.50	46.00	50.60	54.00
65	39.50	32.00	36.60	40.00	94	54.00	46.50	51.10	54.50
66	40.00	32.50	37.10	40.50	95	54.50	47.00	51.60	55.00
67	40.50	33.00	37.60	41.00	96	55.00	47.50	52.10	55.50
68	41.00	33.50	38.10	41.50	97	55.50	48.00	52.60	56.00



深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co.,LTD
电话: 0755-23304126 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		TITLE: 产品名称: FPC0.5间距2.2高掀盖式下接宽版带扣	
X.X ±0.30	X.X* ±3°	APPD: 核准:	PART NO: 产品编号: HDGC0528B-xxCL-GF
X.XX ±0.20	X.XX* ±2°	CHECK: 校对: 王建业	DATE SCALE UNIT CODE NUMBER
X.XXX ±0.10	X.XXX* ±1°	DRAW: 绘图: 黄艳兰	2016-03-12 1:1 mm A001

A

B

C


D

E

F


修订	标记	修改摘要	签名	日期
REV	AO	NEW DWG		2016-03-12

一体覆膜示意图



APPLICABLE FPC/FFC

贴铝箔示意图



APPLICABLE FPC/FFC

NO.of contacts	Dimensions		NO.of contacts	Dimensions	
	B.	E.		B.	E.
40	19.50	24.05	69	34.00	38.55
41	20.00	24.55	70	34.50	39.05
42	20.50	25.05	71	35.00	39.55
43	21.00	25.55	72	35.50	40.05
44	21.50	26.05	73	36.00	40.55
45	22.00	26.55	74	36.50	41.05
46	22.50	27.05	75	37.00	41.55
47	23.00	27.55	76	37.50	42.05
48	23.50	28.05	77	38.00	42.55
49	24.00	28.55	78	38.50	43.05
50	24.50	29.05	79	39.00	43.55
51	25.00	29.55	80	39.50	44.05
52	25.50	30.05	81	40.00	44.55
53	26.00	30.55	82	40.50	45.05
54	26.50	31.05	83	41.00	45.55
55	27.00	31.55	84	41.50	46.05
56	27.50	32.05	85	42.00	46.55
57	28.00	32.55	86	42.50	47.05
58	28.50	33.05	87	43.00	47.55
59	29.00	33.55	88	43.50	48.05
60	29.50	34.05	89	44.00	48.55
61	30.00	34.55	90	44.50	49.05
62	30.50	35.05	91	45.00	49.55
63	31.00	35.55	92	45.50	50.05
64	31.50	36.05	93	46.00	50.55
65	32.00	36.55	94	46.50	51.05
66	32.50	37.05	95	47.00	51.55
67	33.00	37.55	96	47.50	52.05
68	33.50	38.05	97	48.00	52.55



深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD






电话: 0755-23304126 传真: 0755-29940187

-TOLERANCES-
UNLESS OTHERWISE SPECIFIED
公差参数表




TITLE:
产品名称: FPC0.5间距2.2高掀盖式下接宽版带扣

X.X	±0.30	X.X*	±3°	APPD: 核准:	PART NO: 产品编号: HDGC0528B-xxCL-GF			
X.XX	±0.20	X.XX*	±2°	CHECK: 校对: 王建业	DATE	SCALE	UNIT	CODE NUMBER
X.XXX	±0.10	X.XXX*	±1°	DRAW: 绘图: 黄艳兰	2016-03-12	1:1	mm	A001



修订	标记	修改摘要	签名	日期
REV	MARK	REVISION DESCRIPTION	SIGNATURE	DATE
AO		NEW DWG		2016-03-12



NOTES:

- 1.Component load per 13" reel:1500 pcs
- 2.Material: white conductive polystyrene alloy.
- 3.Thickness:0.4±0.05mm
- 4.All dimensions meet EIA-481-C requirements

No.of Contacts	DIM			REEL (CARTON)	SUM(PCS)
	A	B	C		
40pin~52pin	44	20.2	40.4	6	9000
53pin~76pin	44	52.4	26.2	5	7500
77pin~96pin	72	68.4	34.2	4	6000



深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co.,LTD
电话: 0755-23304126 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表				TITLE: 产品名称: FPC0.5间距2.2高掀盖式下接宽版带扣			
X.X	±0.30	X.X*	±3°	APPD: 核准:	PART NO: 产品编号: HDGC0528B~xxCL~GF		
X.XX	±0.20	X.XX*	±2°	CHECK: 校对: 王建业	DATE	SCALE	UNIT
X.XXX	±0.10	X.XXX*	±1°	DRAW: 绘图: 黄艳兰	2016-03-12	1:1	mm