

A

B



C

D




E

F


修订 REV NO	标记 MARK	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE
		NEW DWG		2016-03-12



SECTION: A-A



PCB LAYOUT



APPLICABLE FPC

1.MATERIAL

HOUSING:LCP UL 94V-0

ACTUATOR:LCP UL 94V-0

CONTACTS:COPPER ALLOY

PEG:COPPER ALLOY

2.PLATING:

CONTACTS:TIN OR AU OVER NICKEL

PEG:TIN OVER NICKEL

3.PART NO:

OPERATING VOLTAGE:50V AC,DC

CURRENT RATING:0.3A AC,DC

OPERATING TEMPERATURE:-25°C~+85°C

4.PART NO:

PIN	DIM. A	DIM. B	DIM. C
4	6.10	2.60	1.50
5	6.60	3.10	2.00
6	7.10	3.60	2.50
7	7.60	4.10	3.00
8	8.10	4.60	3.50
9	8.60	5.10	4.00
10	9.10	5.60	4.50
11	9.60	6.10	5.00
12	10.10	6.60	5.50
13	10.60	7.10	6.00
14	11.10	7.60	6.50
15	11.60	8.10	7.00
16	12.10	8.60	7.50
17	12.60	9.10	8.00
18	13.10	9.60	8.50
19	13.60	10.10	9.00
20	14.10	10.60	9.50
21	14.60	11.10	10.00
22	15.10	11.60	10.50
23	15.60	12.10	11.00
24	16.10	12.60	11.50
25	16.60	13.10	12.00
26	17.10	13.60	12.50
27	17.60	14.10	13.00
28	18.10	14.60	13.50
29	18.60	15.10	14.00
30	19.10	15.60	14.50
31	19.60	16.10	15.00
32	20.10	16.60	15.50
33	20.60	17.10	16.00
34	21.10	17.60	16.50
35	21.60	18.10	17.00
36	22.10	18.60	17.50
37	22.60	19.10	18.00
38	23.10	19.60	18.50
39	23.60	20.10	19.00
40	24.10	20.60	19.50
41	24.60	21.10	20.00
42	25.10	21.60	20.50
43	25.60	22.10	21.00
44	26.10	22.60	21.50
45	26.60	23.10	22.00
46	27.10	23.60	22.50
47	27.60	24.10	23.00
48	28.10	24.60	23.50
49	28.60	25.10	24.00
50	29.10	25.60	24.50
51	29.60	26.10	25.00
52	30.10	26.60	25.50
53	30.60	27.10	26.00
54	31.10	27.60	26.50
55	31.60	28.10	27.00
56	32.10	28.60	27.50
59	33.60	30.10	29.00
60	34.10	30.60	29.50
80	44.10	40.60	39.50



深圳市华德共创科技有限公司


Shenzhen Huade co-create Technology Co.,LTD

电话: 0755-23304126 传真: 0755-29940187


-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		TITLE: 产品名称: FPC0.5间距1.5高掀盖下接	
X.X ±0.30	X.X* ±3°	APPD: 核准:	PART NO: 产品编号: HDGC0515-xxCL-CN
X.XX ±0.20	X.XX* ±2°	CHECK: 校对: 王建业	DATE
X.XXX ±0.10	X.XXX* ±1°	DRAW: 绘图: 黄艳兰	SCALE
			UNIT
			CODE NUMBER
		2016-03-12	1:1
			mm
			A001

F		F		F	
修	标	修	修	签	日
订	记	改	改	名	期
REV	MARK	REVISION	DESCRIPTION	SIGNATURE	DATE
AO		NEW	NEW DWG		2016-03-12


REEL DIM



Tape width 16 and 24 mm



Tape width 32 and 56 mm



No.of	DIM				
Contacts	A	B	C	REEL (CARTON)	SUM(PCS)
4pin~8pin	16	7.5	—	15	60000
10pin~24pin	24	11.5	—	10	40000
25pin~35pin	32	14.2	28.4	8	32000
36pin~54pin	44	20.2	40.4	6	24000
55pin~60pin	56	26.25	52.5	5	20000



深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD

电话: 0755-23304126 传真: 0755-29940187

~TOLERANCES~
UNLESS OTHERWISE SPECIFIED
公差参数表



TITLE:
产品名称: FPC0.5间距1.5高掀盖下接

X.X ±0.30 X.X' ±3'

APPD:
核准:

PART NO:
产品编号: HDGC0515-xxCL-CN

X.XX ±0.20 X.XX' ±2'

CHECK:
校对:

王建业

DATE

SCALE

UNIT

CODE NUMBER

X.XXX ±0.10 X.XXX' ±1'

DRAW:
绘图:

黄艳兰

2016-03-12

1:1

mm

A001

NOTES:

- 1.Component load per 13" reel:4000 pcs
- 2.Material: black conductive polystyrene alloy.
- 3.Thickness:0.3±0.05mm
- 4.All dimensions meet EIA-481-C requirements

