

Clipped Sinewave 5 x 3.2 x1.2mm SMD

- Micro-miniature SMD package 5 x 3.2mm
- Stability from ±1ppm over -30° to +75°C
- Supply Voltage from 2.3 Volts to 5.5 Volts
- Produced as TCXO or VCTCXO with EFC
- Readily customized

DESCRIPTION

M53S series TCXOs are ceramic SMD TCXOs packaged in the industry-standard, micro-miniature 5 x 3.2mm package. The TCXO can be run from a supply voltage of 2.3 to 5.5 Volts. Close tolerances from ± 1 ppm over -30° to $+75^{\circ}$ C are available.

SPECIFICATION

Product Series Code:	VM53S
Frequency Range:	10.0MHz to 27.0MHz
Output Waveform:	Clipped Sinewave
Initial Calibration Tolerance*:	<±1ppm at 25°C
Standard Frequencies:	10.0, 12.80, 13.0, 14.40, 15.36, 16.384, 19.2, 19.440, and 19.68MHz (Partial list)
Operating Temperature Range:	See table
Frequency Stability	
vs. Ageing: vs. Voltage Change: vs. Load Change: vs. Reflow:	±1.0 ppm max. first year ±0.3 ppm max. ±5% change ±0.3 ppm max. ±10% change ±1ppm max. for one reflow (Measured after 24 hours)
Supply Voltage:	+2.8, +3.0 or +5.0Volts (Specify when ordering)
Output Voltage Level:	0.8V p-p minimum
Start-up Time:	2ms typical, 5ms max.
Current Consumption:	See table below
Output Load:	$10k\Omega//10pF \pm 10\%$
Harmonic Distortion:	-10dB typical, -7dB max.
SSB Phase Noise:	See table
Output Format:	DC block, AC coupled
Storage Temperature:	-50° to +100°C

^{*} Stability over temperature is measured from this initial frequency.

FREQUENCY STABILITY

Frequency Stability (ppm)		±0.5	±1.0	±1.5	±2.0	±2.5
Temperature Range (°C)	0 ~ +50	ASK	✓	✓	✓	✓
	-10 ~ +60	х	✓	✓	✓	✓
	-20 ~ + 7 0	х	х	✓	✓	✓
	-30 ~ +75	х	x	х	✓	✓
	-40 ~ +85	х	х	х	х	✓

 $[\]sqrt{\ }$ = available, x = not available, ASK = call Technical Sales


CURRENT CONSUMPTION

		Max. Current
Frequency	9.6 to 15MHz	1.5mA
Range	15.01 to 26MHz	2.0mA
	26.01 to 40MHz	2.5mA





M53S - OUTLINE AND DIMENSIONS



VM53S VOLTAGE CONTROL SPECIFICATION

Control Voltage: Standard = $+1.5\pm1.0$ Volts for all input

voltages. (Contact technical sales if

+2.5±2.0 Volts is required.)

Frequency Deviation: ±6.0 ppm min.

Slope Polarity: Positive (increase of control voltage increases

output frequency.)

Input Impedance: $1.0M\Omega$ min.

Modulation Bandwidth: 3.0kHz min. measured at -3dB

Linearity: 10% max.

PHASE NOISE

SSB Phase Noise at 25°C	Offset (Hz)	10	100	1k	10k	100k
	M32S 13MHz (dBc/Hz)	-80	-115	-135	-148	-150

PART NUMBERING PROCEDURE

