




	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		新增脚长尺寸公差, 图面升级整理图面	2024.11.18	阿树





FRONT VIEW



RIGHT SIDE VIEW



BOTTOM VIEW



PCB SIDE TO PHY

PCB SIDE	PHY
1	J1
2	J2
3	J3
4	J4
5	J5
6	J6
7	J7
8	J8

CABLE SIDE

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW: 	MODEL TYPE: RJ JACK		
CHECKED		UNIT: mm/in	PART NO.: X09ADIWA1DY1017		
APPROVED		SIZE: A4	DWG NO.:		
PRECISION CO., LIMITED			SCALE N/A	PAGE 1/1	REVISION A1